

Technical data sheet

Reflector

Part no.: 50124652

HTK 82-24V-8M

Contents

- Technical data
- Electrical connection



Figure can vary

Technical data

Special version

Special version	Heating
-----------------	---------

Electrical data

Performance data

Supply voltage U _B	24 ... 24 V, AC/DC
-------------------------------	--------------------

Connection

Connection 1

Function	Voltage supply
Type of connection	Cable
Cable length	8,000 mm
Sheathing material	PVC
Cable color	Black
Number of conductors	2 -wire

Mechanical data

Design	Round
Mounting dimension, thickness	21 mm
Mounting dimension, diameter	93 mm
Reflection surface diameter	78 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Type of fastening	Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 70 °C
--------------------------------	---------------

Classification

Customs tariff number	39269097
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

Electrical connection

Connection 1

Function	Voltage supply
Type of connection	Cable
Cable length	8,000 mm
Sheathing material	PVC
Cable color	Black
Number of conductors	2 -wire

Pin

Conductor color

1	Blue
2	Brown