

Technical data sheet

Reflector

Part no.: 50136824

MTKS 12x20M.5

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only



Technical data

Basic data

Area of application	Food and pharmaceutical
---------------------	-------------------------

Mechanical data

Design	Rectangular
Triple reflector size	0.3 mm
Mounting dimension, width	17.5 mm
Mounting dimension, height	31 mm
Mounting dimension, thickness	4 mm
Reflective surface, height	20 mm
Reflective surface, width	12 mm
Reflector material	Plastic
Material of base material	Stainless steel
Polarization-changing	Yes
Structure, active surface	Mikrotriple
Net weight	10.5 g
Type of fastening	Through-hole mounting
Compatibility of materials	Alcohol CleanProof+ ECOLAB H2O2

Certifications

Degree of protection	IP 65
	IP 67
	IP 69K

Classification

Customs tariff number	73269098
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Dimensioned drawings

All dimensions in millimeters

