

## Technical data sheet

### Mounting system

Part no.: 50142989

BTU 305M.25-D12

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Basic data

|                            |                          |
|----------------------------|--------------------------|
| Contains                   | 2 M4 x 28 screws         |
|                            | 2 M4 x 8 screws          |
|                            | 2x M3 x 8 screw          |
| Suitable for product group | Switching sensors, cubic |
| Suitable for               | 25C series sensors       |
|                            | 3C series sensors        |
|                            | 46C series sensors       |
|                            | 5 series sensors         |

### Mechanical data

|                                             |                      |
|---------------------------------------------|----------------------|
| Standard designation, metal mounting device | Aluminum             |
|                                             | Steel, galvanized    |
| Design of mounting device                   | Mounting system      |
| Type of fastening, at system                | For 12 mm rod        |
|                                             | Sheet-metal mounting |
| Type of fastening, at device                | Screw type           |
|                                             | Suited for M3 screws |
|                                             | Suited for M4 screws |
| Type of mounting device                     | Adjustable           |
|                                             | Clampable            |
|                                             | Turning, 360°        |
| Mounting device material                    | Metal                |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 83024900 |
| ECLASS 5.1.4          | 27279202 |
| ECLASS 8.0            | 27279202 |
| ECLASS 9.0            | 27273701 |
| ECLASS 10.0           | 27273701 |
| ECLASS 11.0           | 27273701 |
| ECLASS 12.0           | 27273701 |
| ECLASS 13.0           | 27273701 |
| ECLASS 14.0           | 27273701 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |

## Dimensioned drawings

All dimensions in millimeters

