

Technical data sheet

Power supply unit

Part no.: 50155852

NT Base IT 2105i

Contents

- Technical data
- Electrical connection



For illustration purposes only

Technical data

Basic data

Type	Power supply unit
Suitable for	IT 1911i series mobile 2D-code readers

Electrical data

Type	Plug-in power supply unit
Output	5 V DC, 3 A
Input	110 ... 240 V AC, 50 ... 60 Hz

Connection

Number of connections	2 Piece(s)
Connection 1	
Type of connection	Plugs: EU, UK, US, AUS (function: Voltage input)
Connection 2	
Type of connection	Plug: 3.45 mm (function: Voltage output)

Mechanical data

Dimension (W x H x L)	39 mm x 80 mm x 110 mm
Net weight	215 g

Classification

Customs tariff number	85444290
ECLASS 5.1.4	27242611
ECLASS 8.0	27242611
ECLASS 9.0	27242611
ECLASS 10.0	27040701
ECLASS 11.0	27040701
ECLASS 12.0	27040701
ECLASS 13.0	27040701
ECLASS 14.0	27040701
ECLASS 15.0	27040701
ECLASS 16.0	27040701
ETIM 5.0	EC002540
ETIM 6.0	EC002540
ETIM 7.0	EC002540
ETIM 8.0	EC002540
ETIM 9.0	EC002540
ETIM 10.0	EC002540
UNSPSC 26.08	39121004

Electrical connection

Connection 1

Type of connection	Plugs: EU, UK, US, AUS (function: Voltage input)
--------------------	--

Connection 2

Type of connection	Plug: 3.45 mm (function: Voltage output)
--------------------	--