

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<b>Direct Part Mark Reading Mode Setting</b>	<b>DPM Auto Mode - Default</b>  M10375_01 <b>A2</b>	<b>DPM Dark Field (Dot Peen 15-45 Degrees)</b>  M10378_01 <b>A3</b>	<b>DPM Dark Field (Dot Peen 15-45 Degrees/Laser-Etched 90 Degrees)</b>  M10379_01 <b>A4</b>	
	<b>DPM Dark Field (Laser-Etched 90 Degrees)</b>  M10377_01 <b>B1</b>	<b>DPM Diffuse Bright Field (Dot Peen 90 Degrees)</b>  M10382_01 <b>B2</b>	<b>DPM Diffuse Bright Field (Dot Peen/Laser-Etched 90 Degrees)</b>  M10376_01 <b>B3</b>	<b>DPM Diffuse Bright Field (Laser-Etched 90 Degrees)</b>  M10381_01 <b>B4</b>
	<b>DPM Curved Surface Mode (Dot Peen/Laser-Etched 90 Degrees)</b>  M10383_01 <b>C1</b>	<b>DPM Direct Bright Field (Paper Label)</b>  M10380_01 <b>C2</b>	<b>DPM Motion Detection Dark Field - Default</b>  M10384_01 <b>C3</b>	<b>DPM Motion Detection Diffuse Bright Field</b>  M10385_01 <b>C4</b>
	<b>DPM Motion Detection Direct Bright Field</b>  M10386_01 <b>D1</b>	<b>General Reading Mode Settings</b>		<b>Continuous Scan On</b>  M10012_02 <b>D3</b>
<b>Motion Detection On when In Stand and Trigger Out of Stand - Default</b>  M10403_02 <b>E1</b>	<b>Motion Detection On In and Out of Stand</b>  M10404_02 <b>E2</b>	<b>Optimize Motion Detection for Bright Environments - Default</b>  M10014_03 <b>E3</b>	<b>Optimize Motion Detection for Dark Environments</b>  M10015_03 <b>E4</b>	

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>No Motion Detection Delay - Default</p>  <p>M10016_03</p> <p style="text-align: right;"><b>A1</b></p>	<p>500ms Motion Detection Delay</p>  <p>M10017_03</p> <p style="text-align: right;"><b>A2</b></p>	<p>Motion Detection Off In and Out of Stand</p>  <p>M10013_02</p> <p style="text-align: right;"><b>A3</b></p>	<p>Mirroring On</p>  <p>M10125_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>Mirroring Off - Default</p>  <p>M10124_02</p> <p style="text-align: right;"><b>B1</b></p>	<p>Targeting On - Default</p>  <p>M10153_01</p> <p style="text-align: right;"><b>B2</b></p>	<p>Targeting Off</p>  <p>M10154_01</p> <p style="text-align: right;"><b>B3</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>B4</b></p>
<p style="text-align: center;"><b>Data Formatting (Prefix/Suffix) Settings</b></p>	<p>Erase Prefix &amp; Suffix Data - Default</p>  <p>M10135_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>Erase Prefix Data - Default</p>  <p>M10126_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Erase Suffix Data - Default</p>  <p>M10130_01</p> <p style="text-align: right;"><b>C4</b></p>
	<p>Prefix AIM ID On</p>  <p>M10199_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Prefix AIM ID Off - Default</p>  <p>M10198_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Prefix Carriage Return Line Feed (RS232 Mode Only)</p>  <p>M10405_01</p> <p style="text-align: right;"><b>D3</b></p>
<p>Prefix Space</p>  <p>M10128_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>Prefix Tab (USB Keyboard Mode Only)</p>  <p>M10129_01</p> <p style="text-align: right;"><b>E2</b></p>	<p>Prefix Tab (RS232 Mode Only)</p>  <p>M10319_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>Suffix Carriage Return (RS232 Mode Only)</p>  <p>M10320_01</p> <p style="text-align: right;"><b>E4</b></p>





















# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Suffix Carriage Return Line Feed (RS232 Mode Only)</p>  <p>M10322_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>Suffix Comma</p>  <p>M10131_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>Suffix Enter (USB Keyboard Mode Only)</p>  <p>M10134_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>Suffix Line Feed (RS232 Mode Only)</p>  <p>M10321_01</p> <p style="text-align: right;"><b>A4</b></p>	
<p>Suffix Space</p>  <p>M10132_01</p> <p style="text-align: right;"><b>B1</b></p>	<p>Suffix Tab (USB Keyboard Mode Only)</p>  <p>M10133_01</p> <p style="text-align: right;"><b>B2</b></p>	<p>Suffix Tab (RS232 Mode Only)</p>  <p>M10323_01</p> <p style="text-align: right;"><b>B3</b></p>	<p>Translate all Characters to Uppercase On</p>  <p>M10220_03</p> <p style="text-align: right;"><b>B4</b></p>	
<p>Translate all Characters to Uppercase Off - Default</p>  <p>M10426_02</p> <p style="text-align: right;"><b>C1</b></p>	<p><b>Symbology Settings</b></p>		<p>Australian Post On</p>  <p>M10288_02</p> <p style="text-align: right;"><b>C3</b></p>	<p>Australian Post Off - Default</p>  <p>M10289_02</p> <p style="text-align: right;"><b>C4</b></p>
<p>Aztec On - Default</p>  <p>M10018_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Aztec Inverse On</p>  <p>M10020_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Aztec Inverse &amp; Normal On</p>  <p>M10021_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>Aztec Off</p>  <p>M10019_01</p> <p style="text-align: right;"><b>D4</b></p>	
<p>Codabar On - Default</p>  <p>M10022_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>Codabar Off</p>  <p>M10023_01</p> <p style="text-align: right;"><b>E2</b></p>	<p>Codablock F On</p>  <p>M10027_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>Codablock F Off - Default</p>  <p>M10026_01</p> <p style="text-align: right;"><b>E4</b></p>	
















# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Code 11 On</p>  <p>M10029_01</p> <p>A1</p>	<p>Code 11 Off - Default</p>  <p>M10028_01</p> <p>A2</p>	<p>Code 11 Checksum Stripped from Result On</p>  <p>M10031_01</p> <p>A3</p>	<p>Code 32 (Italian Pharmacode) On</p>  <p>M10239_02</p> <p>A4</p>
<p>Code 32 (Italian Pharmacode) Off - Default</p>  <p>M10238_02</p> <p>B1</p>	<p>Code 39 On - Default</p>  <p>M10033_02</p> <p>B2</p>	<p>Code 39 Off</p>  <p>M10034_02</p> <p>B3</p>	<p>Code 39 Checksum On</p>  <p>M10036_01</p> <p>B4</p>
<p>Code 39 Checksum Off - Default</p>  <p>M10035_01</p> <p>C1</p>	<p>Code 39 Checksum Stripped from Result On</p>  <p>M10037_01</p> <p>C2</p>	<p>Code 39 Extended Full ASCII On</p>  <p>M10039_01</p> <p>C3</p>	<p>Code 39 Extended Full ASCII Off - Default</p>  <p>M10038_01</p> <p>C4</p>
<p>Code 49 On</p>  <p>M10458_01</p> <p>D1</p>	<p>Code 49 Off - Default</p>  <p>M10459_01</p> <p>D2</p>	<p>Code 93 On - Default</p>  <p>M10042_01</p> <p>D3</p>	<p>Code 93 Off</p>  <p>M10043_01</p> <p>D4</p>
<p>Code 128 On</p>  <p>M10044_01</p> <p>E1</p>	<p>Code 128 Off</p>  <p>M10045_01</p> <p>E2</p>	<p>Composite On</p>  <p>M10047_01</p> <p>E3</p>	<p>Composite Off - Default</p>  <p>M10046_01</p> <p>E4</p>

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Data Matrix Inverse On - Default</p>  <p>M10051_03</p> <p style="text-align: right;"><b>A1</b></p>	<p>Data Matrix Inverse Off</p>  <p>M10050_03</p> <p style="text-align: right;"><b>A2</b></p>	<p>All GS1 DataBar On - Default</p>  <p>M10054_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>All GS1 DataBar Off</p>  <p>M10055_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>GS1 DataBar Omnidirectional and GS1 DataBar Truncated On</p>  <p>M10057_03</p> <p style="text-align: right;"><b>B1</b></p>	<p>GS1 DataBar Omnidirectional and GS1 DataBar Truncated Off</p>  <p>M10355_02</p> <p style="text-align: right;"><b>B2</b></p>	<p>GS1 DataBar Expanded On</p>  <p>M10059_03</p> <p style="text-align: right;"><b>B3</b></p>	<p>GS1 DataBar Expanded Off</p>  <p>M10417_02</p> <p style="text-align: right;"><b>B4</b></p>
<p>GS1 DataBar Expanded Stacked On</p>  <p>M10357_02</p> <p style="text-align: right;"><b>C1</b></p>	<p>GS1 DataBar Expanded Stacked Off</p>  <p>M10356_02</p> <p style="text-align: right;"><b>C2</b></p>	<p>GS1 DataBar Limited On</p>  <p>M10056_03</p> <p style="text-align: right;"><b>C3</b></p>	<p>GS1 DataBar Limited Off</p>  <p>M10354_02</p> <p style="text-align: right;"><b>C4</b></p>
<p>GS1 DataBar Stacked and GS1 DataBar Stacked Omnidirectional On</p>  <p>M10058_03</p> <p style="text-align: right;"><b>D1</b></p>	<p>GS1 DataBar Stacked and GS1 DataBar Stacked Omnidirectional Off</p>  <p>M10353_03</p> <p style="text-align: right;"><b>D2</b></p>	<p>Han Xin On</p>  <p>M10248_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>Han Xin Off - Default</p>  <p>M10249_01</p> <p style="text-align: right;"><b>D4</b></p>
<p>Hong Kong 2 of 5 On</p>  <p>M10079_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>Hong Kong 2 of 5 Off - Default</p>  <p>M10078_02</p> <p style="text-align: right;"><b>E2</b></p>	<p>Int 2 of 5 On - Default</p>  <p>M10060_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>Int 2 of 5 Off</p>  <p>M10061_01</p> <p style="text-align: right;"><b>E4</b></p>

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Int 2 of 5 Checksum On</p>  <p>M10235_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>Int 2 of 5 Checksum Off</p>  <p>M10234_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>Int 2 of 5 Checksum Stripped from Result On</p>  <p>M10065_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>Japan Post On</p>  <p>M10292_02</p> <p style="text-align: right;"><b>A4</b></p>
<p>Japan Post Off - Default</p>  <p>M10293_02</p> <p style="text-align: right;"><b>B1</b></p>	<p>KIX (Dutch Post) Code On</p>  <p>M10290_02</p> <p style="text-align: right;"><b>B2</b></p>	<p>KIX (Dutch Post) Code Off - Default</p>  <p>M10291_02</p> <p style="text-align: right;"><b>B3</b></p>	<p>Korean Post On</p>  <p>M10358_01</p> <p style="text-align: right;"><b>B4</b></p>
<p>Korean Post Off - Default</p>  <p>M10359_01</p> <p style="text-align: right;"><b>C1</b></p>	<p>Maxicode On</p>  <p>M10067_02</p> <p style="text-align: right;"><b>C2</b></p>	<p>Maxicode Off - Default</p>  <p>M10066_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Matrix 2 of 5 On</p>  <p>M10069_01</p> <p style="text-align: right;"><b>C4</b></p>
<p>Matrix 2 of 5 Off - Default</p>  <p>M10068_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Micro PDF417 On</p>  <p>M10073_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Micro PDF417 Off - Default</p>  <p>M10072_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>MSI Plessey On</p>  <p>M10076_01</p> <p style="text-align: right;"><b>D4</b></p>
<p>MSI Plessey Off - Default</p>  <p>M10077_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>NEC 2 of 5 On</p>  <p>M10082_01</p> <p style="text-align: right;"><b>E2</b></p>	<p>NEC 2 of 5 Off - Default</p>  <p>M10083_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>PDF417 On - Default</p>  <p>M10070_01</p> <p style="text-align: right;"><b>E4</b></p>

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>PDF417 Off</p>  <p>M10071_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>Pharmacode On</p>  <p>M10275_02</p> <p style="text-align: right;"><b>A2</b></p>	<p>Pharmacode Off</p>  <p>M10274_03</p> <p style="text-align: right;"><b>A3</b></p>	<p>Pharmacode Normal Barcode Decoding (Left to Right)</p>  <p>M10281_02</p> <p style="text-align: right;"><b>A4</b></p>
<p>Pharmacode Reverse Barcode Decoding (Right to Left)</p>  <p>M10280_02</p> <p style="text-align: right;"><b>B1</b></p>	<p>All QR Code On</p>  <p>M10101_02</p> <p style="text-align: right;"><b>B2</b></p>	<p>All QR Code Off</p>  <p>M10351_03</p> <p style="text-align: right;"><b>B3</b></p>	<p>Standard QR Code On - Default</p>  <p>M10095_04</p> <p style="text-align: right;"><b>B4</b></p>
<p>Straight 2 of 5 On</p>  <p>M10241_01</p> <p style="text-align: right;"><b>C1</b></p>	<p>Straight 2 of 5 Off - Default</p>  <p>M10240_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>Telepen On</p>  <p>M10103_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Telepen Off - Default</p>  <p>M10104_01</p> <p style="text-align: right;"><b>C4</b></p>
<p>Trioptic On</p>  <p>M10041_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Trioptic Off - Default</p>  <p>M10040_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>UK Plessey On</p>  <p>M10237_02</p> <p style="text-align: right;"><b>D3</b></p>	<p>UK Plessey Off - Default</p>  <p>M10236_02</p> <p style="text-align: right;"><b>D4</b></p>
<p>UK Royal Mail On</p>  <p>M10294_02</p> <p style="text-align: right;"><b>E1</b></p>	<p>UK Royal Mail Off - Default</p>  <p>M10295_02</p> <p style="text-align: right;"><b>E2</b></p>	<p>UPC On - Default</p>  <p>M10105_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>UPC Off</p>  <p>M10106_01</p> <p style="text-align: right;"><b>E4</b></p>

# HCR 6200 Configuration Guide




















NOTE: Configuration changes will take effect immediately and be saved to memory

<p>UPC E Expansion On</p>  <p>M10108_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>UPC E Expansion Off - Default</p>  <p>M10107_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>UPC Supplemental On</p>  <p>M10110_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>UPC Supplemental Off - Default</p>  <p>M10109_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>Transmit UPC-A Check Digit On - Default</p>  <p>M10475_01</p> <p style="text-align: right;"><b>B1</b></p>	<p>Transmit UPC-A Check Digit Off</p>  <p>M10476_01</p> <p style="text-align: right;"><b>B2</b></p>	<p>Transmit UPC-A Number System On - Default</p>  <p>M10477_01</p> <p style="text-align: right;"><b>B3</b></p>	<p>Transmit UPC-A Number System Off</p>  <p>M10478_01</p> <p style="text-align: right;"><b>B4</b></p>
<p>Transmit UPC-E Check Digit On - Default</p>  <p>M10479_01</p> <p style="text-align: right;"><b>C1</b></p>	<p>Transmit UPC-E Check Digit Off</p>  <p>M10480_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>Transmit UPC-E Number System On - Default</p>  <p>M10481_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Transmit UPC-E Number System Off</p>  <p>M10482_01</p> <p style="text-align: right;"><b>C4</b></p>
<p>Transmit EAN-13 Check Digit On - Default</p>  <p>M10483_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Transmit EAN-13 Check Digit Off</p>  <p>M10484_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Transmit EAN-8 Check Digit On - Default</p>  <p>M10485_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>Transmit EAN-8 Check Digit Off</p>  <p>M10486_01</p> <p style="text-align: right;"><b>D4</b></p>
<p>Convert EAN-8 to EAN-13 On</p>  <p>M10488_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>Convert EAN-8 to EAN-13 Off - Default</p>  <p>M10487_01</p> <p style="text-align: right;"><b>E2</b></p>	<p>Convert UPC-A to EAN-13 Off - Default</p>  <p>M10489_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>Convert UPC-A to EAN-13 On</p>  <p>M10490_01</p> <p style="text-align: right;"><b>E4</b></p>



















# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Convert Bookland EAN-13 to ISBN On</p>  <p>M10492_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>Convert Bookland EAN-13 to ISBN Off - Default</p>  <p>M10491_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>Convert Bookland EAN-13 to ISSN On</p>  <p>M10494_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>Convert Bookland EAN-13 to ISSN Off - Default</p>  <p>M10493_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>UPU ID-Tag On</p>  <p>M10360_02</p> <p style="text-align: right;"><b>B1</b></p>	<p>UPU ID-Tag Off - Default</p>  <p>M10361_02</p> <p style="text-align: right;"><b>B2</b></p>	<p>USPS Intelligent Mail/IMB/4-State CB On</p>  <p>M10286_02</p> <p style="text-align: right;"><b>B3</b></p>	<p>USPS Intelligent Mail/IMB/4-State CB Off - Default</p>  <p>M10287_02</p> <p style="text-align: right;"><b>B4</b></p>
<p>USPS Planet On</p>  <p>M10284_02</p> <p style="text-align: right;"><b>C1</b></p>	<p>USPS Postnet Off - Default</p>  <p>M10283_02</p> <p style="text-align: right;"><b>C2</b></p>	<p>USPS Planet Off - Default</p>  <p>M10285_02</p> <p style="text-align: right;"><b>C3</b></p>	<p>USPS Postnet On</p>  <p>M10282_02</p> <p style="text-align: right;"><b>C4</b></p>
<p><b>Keyboard Language Settings</b></p>			
	<p>English (US) Keyboard Mapping for Windows</p>  <p>M10460_02</p> <p style="text-align: right;"><b>D2</b></p>	<p>English (UK) Keyboard Mapping for Windows</p>  <p>M10471_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>Belgian French Keyboard Mapping for Windows</p>  <p>M10461_02</p> <p style="text-align: right;"><b>D4</b></p>
<p>French Keyboard Mapping for Windows</p>  <p>M10462_02</p> <p style="text-align: right;"><b>E1</b></p>	<p>German Keyboard Mapping for Windows</p>  <p>M10463_02</p> <p style="text-align: right;"><b>E2</b></p>	<p>Japanese Keyboard Mapping for Windows</p>  <p>M10464_02</p> <p style="text-align: right;"><b>E3</b></p>	<p>Latin American Keyboard Mapping for Windows</p>  <p>M10465_02</p> <p style="text-align: right;"><b>E4</b></p>




















# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>Spanish Keyboard Mapping for Windows</p>  <p>M10472_01 <b>A1</b></p>	<p>Swiss German Keyboard Mapping for Windows</p>  <p>M10466_02 <b>A2</b></p>	<p>English Keyboard Mapping for Apple</p>  <p>M10419_01 <b>A3</b></p>	<p>Italian Keyboard Mapping for Apple</p>  <p>M10423_01 <b>A4</b></p>
<p>German-Swiss Keyboard Mapping for Apple</p>  <p>M10422_01 <b>B1</b></p>	<p>German Keyboard Mapping for Apple</p>  <p>M10421_01 <b>B2</b></p>	<p>Russian Keyboard Mapping for Windows</p>  <p>M10418_02 <b>B3</b></p>	<p>Control Character Input - Ctrl + Character</p>  <p>M10442_01 <b>B4</b></p>
<p>Control Character Input - Alt + Keypad</p>  <p>M10443_01 <b>C1</b></p>	<p>Control Character Input -Alt + Leading Zero</p>  <p>M10444_01 <b>C2</b></p>	<p>Control Character Input - Language - Default</p>  <p>M10441_01 <b>C3</b></p>	<p>Intentionally Blank</p> <p><b>C4</b></p>
<p><b>Operating System Settings</b></p> <p><b>USB Settings</b></p>	<p>Alternative Operating System (Linux/Mac) On</p>  <p>M10123_02 <b>D2</b></p>	<p>Alternative Operating System (Linux/Mac) Off - Default</p>  <p>M10122_02 <b>D3</b></p>	<p>Intentionally Blank</p> <p><b>D4</b></p>
	<p>Reader - USB Virtual COM CDC Raw Mode</p>  <p>M10438_01 <b>E2</b></p>	<p>Reset to USB Factory Defaults</p>  <p>M10002_02 <b>E3</b></p>	<p>USB Keyboard Mode</p>  <p>M10200_01 <b>E4</b></p>













# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>USB Downloader Mode</p>  <p>M10004_02</p> <p style="text-align: right;"><b>A1</b></p>	<p>USB HID POS Mode (Terminal ID 131)</p>  <p>M10425_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>USB Native Two Way Mode</p>  <p>M10006_02</p> <p style="text-align: right;"><b>A3</b></p>	<p>USB Virtual COM One Way Mode</p>  <p>M10005_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>USB Virtual COM Multiple Ports</p>  <p>M10431_01</p> <p style="text-align: right;"><b>B1</b></p>	<p>USB Virtual COM Common Ports</p>  <p>M10432_01</p> <p style="text-align: right;"><b>B2</b></p>	<p style="text-align: center;"><b>RS232 Settings</b></p>	<p>Reset to RS232 Factory Defaults</p>  <p>M10389_03</p> <p style="text-align: right;"><b>B4</b></p>
<p>RS232 Interface 1200 Baud Rate</p>  <p>M10392_01</p> <p style="text-align: right;"><b>C1</b></p>	<p>RS232 Interface 2400 Baud Rate</p>  <p>M10393_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>RS232 Interface 4800 Baud Rate</p>  <p>M10394_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>RS232 Interface 9600 Baud Rate</p>  <p>M10395_01</p> <p style="text-align: right;"><b>C4</b></p>
<p>RS232 Interface 19200 Baud Rate</p>  <p>M10396_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>RS232 Interface 38400 Baud Rate</p>  <p>M10397_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>RS232 Interface 57600 Baud Rate</p>  <p>M10398_01</p> <p style="text-align: right;"><b>D3</b></p>	<p>RS232 Interface 115200 Baud Rate - Default</p>  <p>M10399_01</p> <p style="text-align: right;"><b>D4</b></p>
<p>RS232 Interface 7 Data Bits</p>  <p>M10390_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>RS232 Interface 8 Data Bits - Default</p>  <p>M10391_01</p> <p style="text-align: right;"><b>E2</b></p>	<p>RS232 Interface Stop Bits 1 - Default</p>  <p>M10406_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>RS232 Interface Stop Bits 2</p>  <p>M10407_01</p> <p style="text-align: right;"><b>E4</b></p>







# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>RS232 Interface Even Parity</p>  <p>M10400_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>RS232 Interface Odd Parity</p>  <p>M10401_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>RS232 Interface No Parity - Default</p>  <p>M10402_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>RS232 Interface Flow Control Off - Default</p>  <p>M10408_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>RS232 Interface Flow Control - Hardware</p>  <p>M10409_01</p> <p style="text-align: right;"><b>B1</b></p>	<p>RS232 Packet Mode</p>  <p>M10388_01</p> <p style="text-align: right;"><b>B2</b></p>	<p>RS232 Raw Mode - Default</p>  <p>M10387_01</p> <p style="text-align: right;"><b>B3</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>B4</b></p>
<p style="text-align: center;"><b>Reader Feedback Settings</b></p>	<p>Beep On Vibrate On - Default</p>  <p>M10140_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>Beep Off Vibrate Off</p>  <p>M10143_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Beep Off Vibrate On</p>  <p>M10141_01</p> <p style="text-align: right;"><b>C4</b></p>
	<p>Beep On Vibrate Off</p>  <p>M10142_01</p> <p style="text-align: right;"><b>D1</b></p>	<p>Beep Volume 100% - Default</p>  <p>M10197_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Beep Volume 67%</p>  <p>M10196_01</p> <p style="text-align: right;"><b>D3</b></p>
<p>Beep Volume 0%</p>  <p>M10194_01</p> <p style="text-align: right;"><b>E1</b></p>	<p style="text-align: center;"><b>Scan Delay Settings</b></p>	<p>Duplicate Scan Disabled - Default</p>  <p>M10144_01</p> <p style="text-align: right;"><b>E3</b></p>	<p>1 Second Duplicate Scan Delay</p>  <p>M10145_01</p> <p style="text-align: right;"><b>E4</b></p>

# HCR 6200 Configuration Guide

NOTE: Configuration changes will take effect immediately and be saved to memory

<p>2 Second Duplicate Scan Delay</p>  <p>M10146_01</p> <p style="text-align: right;"><b>A1</b></p>	<p>3 Second Duplicate Scan Delay</p>  <p>M10147_01</p> <p style="text-align: right;"><b>A2</b></p>	<p>5 Second Duplicate Scan Delay</p>  <p>M10148_01</p> <p style="text-align: right;"><b>A3</b></p>	<p>10 Second Duplicate Scan Delay</p>  <p>M10149_01</p> <p style="text-align: right;"><b>A4</b></p>
<p>30 Second Duplicate Scan Delay</p>  <p>M10150_01</p> <p style="text-align: right;"><b>B1</b></p>	<p>1 Hour Duplicate Scan Delay</p>  <p>M10151_01</p> <p style="text-align: right;"><b>B2</b></p>	<p>1 Day Duplicate Scan Delay</p>  <p>M10152_01</p> <p style="text-align: right;"><b>B3</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>B4</b></p>
<p style="text-align: center;"><b>Reader/Modem Command Settings</b></p>	<p>Reader ID and Firmware Version</p>  <p>M10157_01</p> <p style="text-align: right;"><b>C2</b></p>	<p>Reader Text Commands On</p>  <p>M10137_01</p> <p style="text-align: right;"><b>C3</b></p>	<p>Reader Text Commands Off - Default</p>  <p>M10136_01</p> <p style="text-align: right;"><b>C4</b></p>
	<p>Reset, Clear and Save Reader Settings</p>	<p>Clear All JavaScript Rules</p>  <p>M10139_01</p> <p style="text-align: right;"><b>D2</b></p>	<p>Clear All Stored Data and Images</p>  <p>M10138_02</p> <p style="text-align: right;"><b>D3</b></p>
<p>Reboot Reader</p>  <p>M10296_01</p> <p style="text-align: right;"><b>E1</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>E2</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>E3</b></p>	<p>Intentionally Blank</p> <p style="text-align: right;"><b>E4</b></p>