

Technical data sheet

Attachment lens

Part no.: 50117780

KL-M03

Contents

- Technical data
- Dimensioned drawings
- Accessories



For illustration purposes only

Technical data

Basic data

Contains	2x
----------	----

Functions

Functions	Focusing of light spot
-----------	------------------------

Optical data

Light spot size [at sensor distance]	0.5 mm
--------------------------------------	--------

Focal distance	8 mm
----------------	------

Mechanical data

Net weight	3 g
------------	-----

Type of fastening	Screw type
-------------------	------------

Classification

Customs tariff number	90022000
-----------------------	----------

ECLASS 5.1.4	27279205
--------------	----------

ECLASS 8.0	27279205
------------	----------

ECLASS 9.0	27273602
------------	----------

ECLASS 10.0	27273603
-------------	----------

ECLASS 11.0	27273603
-------------	----------

ECLASS 12.0	27273603
-------------	----------

ECLASS 13.0	27273603
-------------	----------

ECLASS 14.0	27273603
-------------	----------

ECLASS 15.0	27273603
-------------	----------

ECLASS 16.0	27273603
-------------	----------

ETIM 5.0	EC002498
----------	----------

ETIM 6.0	EC003015
----------	----------

ETIM 7.0	EC003015
----------	----------

ETIM 8.0	EC003015
----------	----------



ETIM 9.0	EC003015
----------	----------

ETIM 10.0	EC003015
-----------	----------

UNSPSC 26.08	31241501
--------------	----------

Dimensioned drawings

All dimensions in millimeters



Accessories

General

	Part no.	Designation	Article	Description
	50117758	KFX-ETA-320	Plastic fiber optics type diffuse reflective	Area of application: Highly precise object detection Light beam exit: Front Fiber core: Single fiber core Outer diameter: 1.25 mm Fiber length: 2,000 mm Fiber sheathing material: PE Laying: standard
	50117759	KFX-ETC-320	Plastic fiber optics type diffuse reflective	Area of application: General applications Light beam exit: Front Fiber core: Multiple fiber core, Coaxial fiber configuration Outer diameter: 1.25 mm Fiber length: 2,000 mm Fiber sheathing material: PE Laying: standard
	50117760	KFX-ETD-320	Plastic fiber optics type diffuse reflective	Area of application: Precise object detection Light beam exit: Front Fiber core: Single fiber core Outer diameter: 1.25 mm Fiber length: 2,000 mm Fiber sheathing material: PE Laying: standard

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.