

Technical data sheet

Programming unit

Part no.: 50124709

PA1/XTSX-M12

Contents

- Technical data
- Electrical connection
- Circuit diagrams
- Accessories



For illustration purposes only

Technical data

Basic data

Suitable for	HTU418B
	HTU430B
	LCAM 308

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded

Mechanical data

Dimension (W x H x L)	30 mm x 30 mm x 71 mm
Net weight	72 g
Housing color	Black

Operation and display

Operational controls	Teach button
----------------------	--------------

Classification

Customs tariff number	90329000
ECLASS 5.1.4	27279211
ECLASS 8.0	19200502
ECLASS 9.0	19200502
ECLASS 10.0	19200504
ECLASS 11.0	19200504
ECLASS 12.0	19200504
ECLASS 13.0	19200504
ECLASS 14.0	19200504
ECLASS 15.0	19200504
ECLASS 16.0	19200504
ETIM 5.0	EC001418
ETIM 6.0	EC001418
ETIM 7.0	EC001418
ETIM 8.0	EC001418
ETIM 9.0	EC001418
ETIM 10.0	EC001418

Electrical connection


Connection 1

Function	Connection to device
	Teach input
Type of connection	Connector
Cable length	300 mm
Cable color	Black
Thread size	M12
Type	Female
Material	Plastic
No. of pins	5 -pin
Encoding	A-coded

Connection 2


Function	Connection to device
Type of connection	Connector
Thread size	M12
Type	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Circuit diagrams



Accessories

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50116738 *	K-DS M12A-M8A-4P-0,3m-PVC	Interconnection cable	Application: Chemical resistant Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin Connection 2: Connector, M8, Axial, Male, 4 -pin Shielded: No Cable length: 300 mm Sheathing material: PVC
	50107276 *	K-DS M8A-M12A-4P-0,3m-PVC	Interconnection cable	Application: Chemical resistant Connection 1: Connector, M8, Axial, Female, 4 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 4 -pin Shielded: No Cable length: 300 mm Sheathing material: PVC

* Necessary accessories, please order separately

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.