

## Technical data sheet


### Connection cable

Part no.: 50106977

KB-014S- 10000-14

#### Contents

- Technical data
- Electrical connection



For illustration purposes only



## Technical data

### Basic data

Application	Chemical resistant
-------------	--------------------

### Electrical data

#### Performance data

Operating voltage	30 V AC/DC
-------------------	------------

### Connection

#### Connection 1

Type of connection	Connector
--------------------	-----------

Thread size	M16
-------------	-----

Type	Female
------	--------

No. of pins	14 -pin
-------------	---------

Encoding	A-coded
----------	---------

Version	Angled
---------	--------

Connector, LED	No
----------------	----

#### Connection 2

Type of connection	Open end
--------------------	----------

#### Cable properties

Number of conductors	14 Piece(s)
----------------------	-------------

Shielded	Yes
----------	-----

Cable design	Connection cable (open on one end)
--------------	------------------------------------

Cable diameter (external)	6.7 mm
---------------------------	--------

Cable length	10,000 mm
--------------	-----------

Sheathing material	PVC
--------------------	-----

Suitability for drag chains	No
-----------------------------	----

### Mechanical data

Net weight	575 g
------------	-------

### Operation and display

#### Classification

Customs tariff number	85444290
-----------------------	----------

ECLASS 5.1.4	27279201
--------------	----------

ECLASS 8.0	27279218
------------	----------

ECLASS 9.0	27060311
------------	----------

ECLASS 10.0	27060311
-------------	----------

ECLASS 11.0	27060311
-------------	----------

ECLASS 12.0	27060311
-------------	----------

ECLASS 13.0	27060311
-------------	----------

ECLASS 14.0	27060311
-------------	----------

ECLASS 15.0	27060311
-------------	----------

ECLASS 16.0	27060311
-------------	----------

ETIM 5.0	EC001855
----------	----------

ETIM 6.0	EC001855
----------	----------

ETIM 7.0	EC001855
----------	----------

ETIM 8.0	EC001855
----------	----------

ETIM 9.0	EC001855
----------	----------

ETIM 10.0	EC001855
-----------	----------

UNSPSC 26.08	26121604
--------------	----------

## Electrical connection

### Connection 1

Type of connection	Connector
--------------------	-----------

Thread size	M16
-------------	-----

Type	Female
------	--------

No. of pins	14 -pin
-------------	---------

Encoding	A-coded
----------	---------

Version	Angled
---------	--------

Connector, LED	No
----------------	----

### Connection 2

Type of connection	Open end
--------------------	----------