

## Technical data sheet

### Mounting bracket

Part no.: 50009419

BT 910M

#### Contents

- Technical data
- Dimensioned drawings
- Accessories



For illustration purposes only

Technical data

Basic data

|                            |            |
|----------------------------|------------|
| Suitable for product group | Reflectors |
|----------------------------|------------|

Mechanical data


|                                             |                       |
|---------------------------------------------|-----------------------|
| Standard designation, metal mounting device | Aluminum              |
| Design of mounting device                   | Angle, L-shape        |
| Type of fastening, at system                | Through-hole mounting |
| Type of fastening, at device                | Screw type            |
| Type of mounting device                     | Rigid                 |
| Mounting device material                    | Metal                 |

Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 73182900 |
| ECLASS 5.1.4          | 27279202 |
| ECLASS 8.0            | 27279202 |
| ECLASS 9.0            | 27273701 |
| ECLASS 10.0           | 27273701 |
| ECLASS 11.0           | 27273701 |
| ECLASS 12.0           | 27273701 |
| ECLASS 13.0           | 27273701 |
| ECLASS 14.0           | 27273701 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |

Dimensioned drawings

All dimensions in millimeters



Accessories

Standard reflectors

|                                                                                   | Part no. | Designation | Article   | Description                                                                                                                                                                                                                  |
|-----------------------------------------------------------------------------------|----------|-------------|-----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50003192 | TK 100x100  | Reflector | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 96 mm x 96 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Rear side can be glued  |
|  | 50022811 | TK 40X180.1 | Reflector | Design: Rectangular<br>Triple reflector size: 3 mm<br>Reflective surface: 36 mm x 176 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Rear side can be glued |
|  | 50003191 | TK 50x100   | Reflector | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 46 mm x 96 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Rear side can be glued  |

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.