

## Technical data sheet

### Connection cable

Part no.: 50154367

KB 4AC1 010

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection

For illustration purposes only



## Technical data

### Basic data

|                        |                             |
|------------------------|-----------------------------|
| Application            | Oil and lubricant resistant |
| Suitable for interface | RS 232                      |

### Electrical data

|                   |            |
|-------------------|------------|
| Performance data  |            |
| Operating voltage | 30 V AC/DC |

### Connection

|                             |                                    |
|-----------------------------|------------------------------------|
| Connection 1                |                                    |
| Type of connection          | JST ZHR connector                  |
| No. of pins                 | 4 -pin                             |
| Connector, LED              | No                                 |
| Connection 2                |                                    |
| Type of connection          | Open end                           |
| Cable properties            |                                    |
| Number of conductors        | 4 Piece(s)                         |
| Sheathing color             | Black                              |
| Shielded                    | No                                 |
| Cable design                | Connection cable (open on one end) |
| Cable diameter (external)   | 3.95 mm                            |
| Cable length                | 1,000 mm                           |
| Sheathing material          | PVC                                |
| Suitability for drag chains | Yes                                |

### Mechanical data

|                |                    |
|----------------|--------------------|
| Net weight     | 99 g               |
| Bending cycles | 5,000,000 Piece(s) |


### Operation and display

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |

## Dimensioned drawings

All dimensions in millimeters



## Electrical connection

### Connection 1

|                    |                   |
|--------------------|-------------------|
| Type of connection | JST ZHR connector |
| No. of pins        | 4 -pin            |
| Connector, LED     | No                |

### Connection 2

|                    |          |
|--------------------|----------|
| Type of connection | Open end |
|--------------------|----------|