

## Technisches Datenblatt

### Aufkleber

Art.-Nr.: 50120359

Safety Sticker Set 2

#### Inhalt

- Technische Daten

#### Leuze

**Regular function test of the protective device by instructed persons (e.g. operators)**

The following tests are carried out on a regular basis (e.g. daily). Make absolutely certain that no persons are located in the danger zone during the inspection.

##### Test at least:

- ☞ Are safety sensor and connectors securely mounted and free of obvious signs of damage, changes or tampering?
- ☞ Are possible access points free from obvious signs of modification?
- ☞ Test the effectiveness of the safety sensor:
  1. The OSSD LED on the safety sensor must illuminate green.
  2. Interrupt an active beam or the protective field with a suitable, opaque test object.
  3. Does the OSSD LED illuminate constantly red while the protective field is interrupted?

##### When possible, test during running operation:

- Protective device with approach function:  
during machine operation, the protective field is interrupted with a suitable opaque test object - are the obviously dangerous machine parts stopped without noticeable delay?
- Protective device with presence detection:  
the protective field is interrupted with a suitable opaque test object - does this prevent operation of the obviously dangerous machine parts?

If there is any doubt about the correct function of the safety system or if you answer no to one of the points, shutdown the system and inform the person responsible. More information about regular testing of the safety sensors can be found in the respective operating instructions.

##### Cleaning:

In the event of visible contamination, the front screens of the AOPDs are to be periodically cleaned with mild detergent. Do not use abrasive, alcohol-containing or aggressive detergents or solvents!

EN - 06/2024 Art.-No. 50120359-02

Abbildung kann abweichen

## Technische Daten

### Basisdaten

<b>Beschreibung</b>	Sicherheitshinweise "Regelmäßige Funktionsprüfung der Schutzeinrichtung"
<b>Details</b>	Haftetiketten, 12 Blatt in einem Polybeutel

### Mechanische Daten

<b>Abmessung (B x H x L)</b>	100 mm x 210 mm
<b>Nettogewicht</b>	43 g
<b>Werkstoff</b>	Silber kaschiertes Haftpapier matt, permanent haftend

### Software

<b>Sprachen</b>	Bulgarisch
	Dänisch
	Estnisch
	Finnisch
	Griechisch
	Kroatisch
	Lettisch
	Litauisch
	Niederländisch
	Rumänisch
	Slowakisch
	Slowenisch
	Ungarisch

### Klassifikation

<b>Zolltarifnummer</b>	48114190
<b>ECLASS 5.1.4</b>	27279290
<b>ECLASS 8.0</b>	27279290
<b>ECLASS 9.0</b>	27279090
<b>ECLASS 10.0</b>	27273692
<b>ECLASS 11.0</b>	27273692
<b>ECLASS 12.0</b>	27273692
<b>ECLASS 13.0</b>	27273692
<b>ECLASS 14.0</b>	27273692
<b>ECLASS 15.0</b>	27273692
<b>ECLASS 16.0</b>	27273692
<b>ETIM 5.0</b>	EC002498
<b>ETIM 6.0</b>	EC003015
<b>ETIM 7.0</b>	EC003015
<b>ETIM 8.0</b>	EC003015
<b>ETIM 9.0</b>	EC003015
<b>ETIM 10.0</b>	EC003015
<b>UNSPSC 26.08</b>	31242100