

Technisch gegevensblad Zelfklevend etiket

Art.-nr.: 50142923

Safety Sticker Set

Inhoud

- Technische gegevens

Leuze electronic

Regular function test of the protective device by instructed persons (e.g. operators)

The following tests are carried out on a regular basis (e.g.: daily).
Make absolutely certain that no persons are located in the danger zone during the inspection.

Test at least:

- ↳ Are safety sensor and connectors securely mounted and free of obvious signs of damage, changes or tampering?
- ↳ Are possible access points free from obvious signs of modification?
- ↳ Test the effectiveness of the safety sensor:
 1. The OSSD LED on the safety sensor must illuminate green.
 2. Interrupt an active beam or the protective field with a suitable, opaque test object.
 3. Does the OSSD LED illuminate constantly red while the protective field is interrupted?

When possible, test during running operation:

- ☐ Protective device with approach function:
during machine operation, the protective field is interrupted with a suitable opaque test object – are the obviously dangerous machine parts stopped without noticeable delay?
- ☐ Protective device with presence detection:
the protective field is interrupted with a suitable opaque test object – does this prevent operation of the obviously dangerous machine parts?

If there is any doubt about the correct function of the safety system or if you answer no to one of the points, shutdown the system and inform the person responsible.

More information about regular testing of the safety sensors can be found in the respective operating instructions.

Cleaning:

In the event of visible contamination, the front screens of the AOPDs are to be periodically cleaned with mild detergent. Do not use abrasive, alcohol-containing or aggressive detergents or solvents!

Afbeelding kan afwijken

Technische gegevens

Basisgegevens

Beschrijving	Veiligheidsaanwijzing "Regelmatische controle van de werking van de beveiligingsinrichting"
Details	Plaketiketten, 13 bladen in een kunststofhoes

Mechanische gegevens

Afmeting (b x h x l)	100 mm x 210 mm
Nettogewicht	35 g
Materiaal	Zilver gelamineerd stickerpapier mat, permanent zelfklevend

Software

Talen	Chinees (vereenvoudigd)
	Duits
	Engels
	Frans
	Italiaans
	Koreaans
	Pools
	Portugees
	Russisch
	Spaans
	Tsjechisch
	Turks
	Zweeds

Classificatie

Douanetariefnummer	48114190
ECLASS 5.1.4	27279290
ECLASS 8.0	27279290
ECLASS 9.0	27279090
ECLASS 10.0	27273692
ECLASS 11.0	27273692
ECLASS 12.0	27273692
ECLASS 13.0	27273692
ECLASS 14.0	27273692
ECLASS 15.0	27273692
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015
ETIM 10.0	EC003015