

Technical data sheet

Plastic fiber optics for throughbeam operation

Part no.: 50152665

KF-L-100MLF-02

Contents

- Technical data
- Dimensioned drawings
- Notes
- Further information



For illustration purposes only

Technical data

Basic data

Series	KF
Operating principle	Throughbeam principle
Device type	Transmit and receive fiber
Area of application	General applications

Special version

Special version	Area detection
-----------------	----------------

Optical data

Light beam exit	Lateral
Fiber core	Mixed fiber configuration Multiple fiber core
Fiber core material	Plastic
Active fiber diameter	0.265 mm x 32 Piece(s)
Operating range with LV461	0 ... 300 mm
Operating range with LV462	0 ... 440 mm
Operating range with LV463	0 ... 440 mm
Operating range with LV463.XV	0 ... 440 mm
Operating range with LV463.XR	0 ... 440 mm
Operating range with LV463L.XR	0 ... 440 mm

Measurement data

Minimum object diameter	3.5 mm
-------------------------	--------

Mechanical data

Design	Cubic
Outer diameter	2.8 mm
Net weight	85 g
Head material	Zinc
Type	Plastic fiber optics (KF)
Fiber length	210 mm
Light field width	100 mm
Fiber sheathing material	PE
Fastening of the probe	2 x Ø 4.1 mm
Smallest bending radius (moving)	R60
Laying	standard
Damping at $\lambda = 650\text{nm}$	210 dB/km

Environmental data

Ambient temperature, operation	-55 ... 70 °C
--------------------------------	---------------

Classification

Customs tariff number	90011090
ECLASS 5.1.4	27270905
ECLASS 8.0	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905
ECLASS 11.0	27273606
ECLASS 12.0	27273606
ECLASS 13.0	27273606
ECLASS 14.0	27273606
ECLASS 15.0	27273606
ECLASS 16.0	27273606
ETIM 5.0	EC002651
ETIM 6.0	EC002651
ETIM 7.0	EC002651
ETIM 8.0	EC002651
ETIM 9.0	EC002651
ETIM 10.0	EC002651
UNSPSC 26.08	41112103

Further information

- Suitable products for operating these fiber optics are the fiber optic amplifiers LV461, LV462B as well as LV463, LV463.XV and LV463.XR.
- The maximum range is limited by the length of the light conductor.
- Operating range measured on a white object (90% diffuse reflection) with the following settings on the fiber optic amplifier:
 - max. response time
 - max. amplification
 - min. switching threshold