

Karta danych technicznych Element mocujący

Nr art.: 50154483

BT DCR 100

Treść

- Dane techniczne
- Rysunki wymiarowe



Ilustracja może się różnić od stanu rzeczywistego

Dane techniczne

Dane podstawowe

Odpowiednie dla grupy produktów	Stacjonarne czytniki kodów kreskowych
Przeznaczony dla	Czytniki kodów kreskowych serii DCR 1xxi Lustra odbijające

Dane mechaniczne

Oznaczenie standardowe elementu mocującego z metalu	Stal nierdzewna (SUS304)
Wersja elementu mocującego	Kątowniki kształt L
Rodzaj mocowania, po stronie instalacji	Mocowanie przelotowe
Rodzaj mocowania, po stronie urządzenia	przykręcany
Rodzaj elementu mocującego	szttywne
Materiał elementu mocującego	Metal

Klasyfikacja

Numer taryfy celnej	73182900
ECLASS 5.1.4	27279202
ECLASS 8.0	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ECLASS 13.0	27273701
ECLASS 14.0	27273701
ECLASS 15.0	27273701
ECLASS 16.0	27273701
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015
ETIM 10.0	EC003015
UNSPSC 26.08	31242100

Technical drawing of a mechanical part, likely a flange or end plate, showing front and side views with dimensions.

Front View Dimensions:

- Overall width: 50.0
- Overall height: 49.2
- Top edge features: 5.6, 5.0, 14.0, 5.0
- Bottom edge features: 11.6, 13.0, 13.0
- Central circular features: 8-R1.6 (outer), 4-Ø3.2 (inner), Ø38.0 (diameter)
- Internal radial features: 8-R1.6
- Internal vertical dimensions: 19.0, 13.0, 13.0

Side View Dimensions:

- Overall thickness: 1.5
- Internal vertical dimensions: 12.5, 12.5

