

Technical data sheet

Acoustic indicator

Part no.: 50130532

PBZ-V1-065

Contents

- Technical data
- Electrical connection
- Notes



Figure can vary



Technical data

Basic data

Type of signaling	Acoustic
-------------------	----------

Electrical data

Performance data

Supply voltage U_B	12 ... 24 V, AC/DC
Current consumption, max.	46 mA

Connection

Connection 1

Type of connection	Terminal
--------------------	----------

Mechanical data

Design	Cylindrical
Dimension (\varnothing x L)	30 mm x 59 mm
Length in installed state	12 mm
Housing material	Plastic
Net weight	30 g
Housing color	Black
Type of fastening, at system	In bore holes with \varnothing 22.5 mm

Environmental data

Ambient temperature, operation	-20 ... 60 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 65
Certifications	c UL US

Acoustic data

Tone type	Continuous or pulse tone
Audio frequency	Approx. 3500 Hz
Sound pressure	65 dB
Number of tones	2

Classification

Customs tariff number	85318070
eCl@ss 5.1.4	27371214
eCl@ss 8.0	27371214
eCl@ss 9.0	27371214
eCl@ss 10.0	27371214
eCl@ss 11.0	27371214
ETIM 5.0	EC001026
ETIM 6.0	EC001026
ETIM 7.0	EC001026

Electrical connection

Connection 1

Type of connection	Terminal
Type of terminal	Removable screw terminals

Notes



Observe intended use!



- ⚠ This product is not a safety sensor and is not intended as personnel protection.
- ⚠ The product may only be put into operation by competent persons.
- ⚠ Only use the product in accordance with its intended use.



For UL applications:



- ⚠ For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).