

## Technical data sheet

### Polarized retro-reflective photoelectric sensor

Part no.: 50134447

PRK49C.1/4P-TB



For illustration purposes only

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Reflectors & reflective tapes
- Part number code
- Notes
- Further information
- Accessories



## Technical data

### Basic data

|                     |                      |
|---------------------|----------------------|
| Series              | 49C                  |
| Operating principle | Reflection principle |

### Optical data

|                                      |                                                                         |
|--------------------------------------|-------------------------------------------------------------------------|
| Operating range                      | 0.1 ... 24 m (guaranteed operating range), With reflector TK(S) 100x100 |
| Operating range limit                | 0.1 ... 30 m (typical operating range), With reflector TK(S) 100x100    |
| Beam path                            | Divergent                                                               |
| Light source                         | LED, Red                                                                |
| Wavelength                           | 630 nm                                                                  |
| Transmitted-signal shape             | Pulsed                                                                  |
| LED group                            | Exempt group (in acc. with EN 62471)                                    |
| Light spot size [at sensor distance] | 130 mm [6,000 mm]                                                       |
| Type of light spot geometry          | Round                                                                   |

### Electrical data

|                    |                                                                                 |
|--------------------|---------------------------------------------------------------------------------|
| Protective circuit | Polarity reversal protection<br>Short circuit protected<br>Transient protection |
|--------------------|---------------------------------------------------------------------------------|

### Performance data

|                           |                                        |
|---------------------------|----------------------------------------|
| Supply voltage $U_B$      | 10 ... 30 V, DC, Incl. residual ripple |
| Current consumption, max. | 100 mA                                 |
| Residual ripple           | 0 ... 15 %, From $U_B$                 |
| Open-circuit current      | 0 ... 20 mA                            |

### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 2 Piece(s) |
|-------------------------------------|------------|

### Switching outputs

|                         |                                           |
|-------------------------|-------------------------------------------|
| Type                    | Digital switching output                  |
| Voltage type            | DC                                        |
| Switching current, max. | 100 mA                                    |
| Switching voltage       | high: $\geq(U_B - 2V)$<br>low: $\leq 2 V$ |

### Switching output 1

|                     |                     |
|---------------------|---------------------|
| Assignment          | Connection 1, pin 3 |
| Switching element   | Transistor, PNP     |
| Switching principle | Light switching     |

### Switching output 2

|                     |                     |
|---------------------|---------------------|
| Assignment          | Connection 1, pin 4 |
| Switching element   | Transistor, PNP     |
| Switching principle | Dark switching      |

### Time behavior

|                     |        |
|---------------------|--------|
| Switching frequency | 500 Hz |
| Response time       | 1 ms   |
| Readiness delay     | 300 ms |

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

### Connection 1

|                    |                              |
|--------------------|------------------------------|
| Function           | Signal OUT<br>Voltage supply |
| Type of connection | Terminal                     |
| Type of terminal   | Spring-cage terminal         |
| No. of pins        | 5 -pin                       |

### Mechanical data

|                       |                                                       |
|-----------------------|-------------------------------------------------------|
| Dimension (W x H x L) | 31 mm x 104 mm x 55.5 mm                              |
| Housing material      | Plastic                                               |
| Plastic housing       | PC                                                    |
| Lens cover material   | Plastic                                               |
| Net weight            | 150 g                                                 |
| Housing color         | Red                                                   |
| Type of fastening     | Through-hole mounting<br>Via optional mounting device |

### Operation and display

|                                     |                                                                                                   |
|-------------------------------------|---------------------------------------------------------------------------------------------------|
| Type of display                     | LED                                                                                               |
| Number of LEDs                      | 2 Piece(s)                                                                                        |
| Operational controls                | 270° potentiometer<br>Teach button                                                                |
| Function of the operational control | Activation of the time module for dropout delay<br>Light/dark switching<br>Sensitivity adjustment |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 60 °C |
| Ambient temperature, storage   | -40 ... 70 °C |


### Certifications

|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
| Protection class     | II            |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270902 |
| ECLASS 8.0            | 27270902 |
| ECLASS 9.0            | 27270902 |
| ECLASS 10.0           | 27270902 |
| ECLASS 11.0           | 27270902 |
| ECLASS 12.0           | 27270902 |
| ECLASS 13.0           | 27270902 |
| ECLASS 14.0           | 27270902 |
| ECLASS 15.0           | 27270902 |
| ETIM 5.0              | EC002717 |
| ETIM 6.0              | EC002717 |
| ETIM 7.0              | EC002717 |
| ETIM 8.0              | EC002717 |
| ETIM 9.0              | EC002717 |
| ETIM 10.0             | EC002717 |

All dimensions in millimeters




## Connection 1


| Terminal | Assignment |
|----------|------------|
| 1        | V+         |
| 2        | GND        |
| 3        | OUT 1      |
| 4        | OUT 2      |
| 5        | n.c.       |

Diagrams

Typ. response behavior (TKS100x100)



Typ. function reserve



Operation and display

| LED | Display                  | Meaning                              |
|-----|--------------------------|--------------------------------------|
| 1   | Green, continuous light  | Operational readiness                |
| 2   | Yellow, continuous light | Light path free                      |
|     | Yellow, flashing         | Light path free, no function reserve |

Reflectors & reflective tapes

|                                                                                     | Part no. | Designation  | Operating range<br>Operating range<br>limit | Description                                                                                                                                                                                                                            |
|-------------------------------------------------------------------------------------|----------|--------------|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50117583 | MTKS 50x50.1 | 0.3 ... 15 m<br>0.1 ... 18 m                | Design: Rectangular<br>Triple reflector size: 1.2 mm<br>Reflective surface: 50 mm x 50 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive |

## Reflectors & reflective tapes

|                                                                                     | Part no. | Designation   | Operating range<br>Operating range<br>limit | Description                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------|----------|---------------|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | 50108300 | REF 4-A-50x50 | 0.3 ... 4 m<br>0.1 ... 5 m                  | Design: Rectangular<br>Reflective surface: 50 mm x 50 mm<br>Material: Plastic<br>Chemical designation of the material: PMMA<br>Fastening: Self-adhesive                                                                                        |
|    | 50003189 | TK 30x50      | 0.3 ... 12 m<br>0.1 ... 15 m                | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 29 mm x 45 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Rear side can be glued                    |
|    | 50024127 | TK 82.2       | 0.3 ... 15 m<br>0.1 ... 18 m                | Design: Round<br>Triple reflector size: 4 mm<br>Reflective surface, diameter: 79 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Rear side can be glued |
|   | 50022816 | TKS 100X100   | 0.3 ... 24 m<br>0.1 ... 30 m                | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 96 mm x 96 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive           |
|  | 50081283 | TKS 20X40     | 0.3 ... 8 m<br>0.1 ... 10 m                 | Design: Rectangular<br>Triple reflector size: 2.3 mm<br>Reflective surface: 16 mm x 38 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive         |
|  | 50023525 | TKS 30X50     | 0.3 ... 12 m<br>0.1 ... 15 m                | Design: Rectangular<br>Triple reflector size: 3 mm<br>Reflective surface: 27 mm x 44 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive           |

## Part number code

Part designation: AAA49Cd.EEfG/IJ-KL

|        |                                                                                                                                                                                                                                                                                                |
|--------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AAA49C | <b>Operating principle / construction</b><br>PRK49C: Retro-reflective photoelectric sensor with polarization filter<br>HT49C: Diffuse reflection sensor with background suppression<br>LS49C: Throughbeam photoelectric sensor transmitter<br>LE49C: Throughbeam photoelectric sensor receiver |
| d      | <b>Light type</b><br>n/a: red light<br>I: infrared light                                                                                                                                                                                                                                       |
| EE     | <b>Operating voltage</b><br>n/a: 10 ... 30 V, DC<br>UC: 20 ... 250V AC/DC (all-mains design)                                                                                                                                                                                                   |

Part number code

|    |                                                                                                                                                                                                                                                                                                                                                                                    |
|----|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| f  | <b>Equipment</b><br>H: with heating<br>D: Depolarizing media<br>1: 270° potentiometer<br>8: activation input (activation with high signal)                                                                                                                                                                                                                                         |
| iJ | <b>Switching output / Function / OUT1OUT2</b><br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>W: warning output<br>TS: Relay, NC contact/NO contact<br>M4: Low impedance MOSFET semiconductor switching output, NO contact<br>X: pin not used |
| KL | <b>Electrical connection</b><br>TB: Terminal block - terminal compartment with spring terminals (5 x 1.5mm²)<br>n/a: cable, standard length 2000mm<br>M12: M12 connector, 4-pin (plug)                                                                                                                                                                                             |

| Note                                                                             |                                                                                                                                        |
|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>↪ A list with all available device types can be found on the Leuze website at <a href="http://www.leuze.com">www.leuze.com</a>.</p> |

Notes

|  Observe intended use! |                                                                                                                                                                                                                                        |
|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                         | <p>↪ This product is not a safety sensor and is not intended as personnel protection.</p> <p>↪ The product may only be put into operation by competent persons.</p> <p>↪ Only use the product in accordance with its intended use.</p> |

| For UL applications:                                                               |                                                                                                                                                                                                                                                                                                                    |
|------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>↪ For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).</p> <p>↪ These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)</p> |

Further information

- All-insulated, rating voltage 250 VAC
- Light source: Average life expectancy 100,000 h at an ambient temperature of 25 °C

## Accessories

## Mounting technology - Mounting brackets

|                                                                                   | Part no. | Designation | Article         | Description                                                                                                                                                                              |
|-----------------------------------------------------------------------------------|----------|-------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50025570 | BT 96       | Mounting device | Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Rigid<br>Material: Metal |

## Mounting technology - Rod mounts

|                                                                                   | Part no. | Designation  | Article         | Description                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------|----------|--------------|-----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50128380 | BTU 460M-D12 | Mounting system | Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Adjustable, Turning, 360°<br>Material: Metal |

## Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.