# Technical data sheet
# Capacitive sensor
Part no.: 50151579
LCS-2Q54P-N10PNC-K020P



For Illustration purposes only

**Contents**


- Technical data
- Dimensioned drawings
- Electrical connection
- Circuit diagrams
- Operation and display
- Part number code
- Notes

# Technical data

Leuze

## Basic data

| | |
|---|---|
| **Series** | LCS-2 |
| **Switching distance $S_n$** | 1 ... 10 mm |

## Characteristic parameters

| | |
|---|---|
| **MTTF** | 563 years |

## Electrical data

| | |
|---|---|
| **Protective circuit** | Overvoltage protection |
| | Polarity reversal protection |
| | Short circuit protected |

### Performance data

| | |
|---|---|
| **Supply voltage $U_B$** | 10 ... 30 V, DC |
| **Residual ripple** | 0 ... 10 %, From $U_B$ |
| **Open-circuit current** | 20 mA |
| **Temperature drift, max. (in % of $S_r$)** | 15 % |
| **Repeatability, max. (in % of $S_r$)** | 5 % |
| **Rated operating current** | 200 mA |

### Outputs

| | |
|---|---|
| **Number of digital switching outputs** | 1 Piece(s) |

#### Switching outputs

| | |
|---|---|
| **Type** | Digital switching output |
| **Voltage type** | DC |

##### Switching output 1

| | |
|---|---|
| **Assignment** | Connection 1, conductor 2 |
| **Switching element** | Transistor, PNP |
| **Switching principle** | NC (normally closed) |

## Time behavior

| | |
|---|---|
| **Switching frequency** | 100 Hz |

## Connection

| | |
|---|---|
| **Number of connections** | 1 Piece(s) |

### Connection 1

| | |
|---|---|
| **Function** | Signal OUT |
| | Voltage supply |
| **Type of connection** | Cable |
| **Cable length** | 2,000 mm |
| **Sheathing material** | PUR |
| **Number of conductors** | 3 -wire |
| **Wire cross section** | 0.18 mm² |

## Mechanical data

| | |
|---|---|
| **Design** | Cubic |
| **Dimension (W x H x L)** | 50 mm x 20 mm x 5.5 mm |
| **Type of installation** | Non-embedded/non-flush |
| **Housing material** | Plastic |
| **Plastic housing** | ABS |
| **Sensing face material** | ABS, ABS |
| **Cover material** | Plastic |
| **Net weight** | 44 g |

## Operation and display

| | |
|---|---|
| **Type of display** | LED |
| **Number of LEDs** | 2 Piece(s) |
| **Operational controls** | Multiturn potentiometer (12 turns) |
| **Function of the operational control** | Sensitivity adjustment |
| **Switching distance, adjustable** | Yes |

## Environmental data

| | |
|---|---|
| **Ambient temperature, operation** | -25 ... 70 °C |

## Certifications

| | |
|---|---|
| **Degree of protection** | IP 65 |
| **Protection class** | III |
| **Standards applied** | IEC 60947-5-2 |

## Correction factors


| | |
|---|---|
| **Acetone** | 0.75 |
| **Acrylic resin** | 0.1 ... 0.25 |
| **Alcohol** | 0.85 |
| **Ammonia** | 0.7 ... 0.85 |
| **Aniline** | 0.4 |
| **Gasoline** | 0.1 |
| **Celluloid** | 0.15 |
| **Liquid chlorine** | 0.1 |
| **Ebonite** | 0.15 |
| **Epoxy resin** | 0.15 ... 0.35 |
| **Crude oil** | 0.05 |
| **Ethanol** | 0.85 |
| **Ethylene glycol** | 0.93 |
| **Freon R22 and 502 (liquid)** | 0.35 |
| **Grain** | 0.15 ... 0.3 |
| **Glass** | 0.2 ... 0.55 |
| **Glycerin** | 0.98 |
| **Rubber** | 0.15 ... 0.9 |
| **Wood, wet** | 0.6 ... 0.85 |
| **Wood, dry** | 0.1 ... 0.4 |
| **Carbon dioxide** | 0 |
| **Air** | 0 |
| **Marble** | 0.5 |
| **Flour** | 0.05 |
| **Melamine resin** | 0.25 ... 0.55 |
| **Milk powder** | 0.2 |
| **Nylon** | 0.2 ... 0.3 |
| **Oil-containing paper** | 0.25 |
| **Paper** | 0.1 |
| **Polyamide** | 0.3 |
| **Polyester resin** | 0.15 ... 0.5 |
| **Pressboard** | 0.1 ... 0.3 |
| **PTFE** | 0.1 |
| **Quartz glass** | 0.2 |
| **Salt** | 0.35 |
| **Sand** | 0.15 ... 0.3 |
| **Water** | 1 |
| **Cement dust** | 0.25 |
| **Sugar** | 0.15 |

# Technical data

| | |
|---|---|
| **Customs tariff number** | 85365019 |
| **ECLASS 5.1.4** | 27270102 |
| **ECLASS 8.0** | 27270102 |
| **ECLASS 9.0** | 27270102 |
| **ECLASS 10.0** | 27270102 |
| **ECLASS 11.0** | 27270102 |
| **ECLASS 12.0** | 27274201 |
| **ECLASS 13.0** | 27274201 |
| **ECLASS 14.0** | 27274201 |
| **ECLASS 15.0** | 27274201 |
| **ECLASS 16.0** | 27274201 |
| **ETIM 5.0** | EC002715 |
| **ETIM 6.0** | EC002715 |
| **ETIM 7.0** | EC002715 |
| **ETIM 8.0** | EC002715 |
| **ETIM 9.0** | EC002715 |
| **ETIM 10.0** | EC002715 |
| **UNSPSC 26.08** | 39122230 |

# Dimensioned drawings


All dimensions in millimeters




A Active surface


# Dimensioned drawings

## Mounting variants



# Dimensioned drawings

## Mounting distances




| | | | |
|---|---|---|---|
| B | Ø 20 mm, diameter of the active surface | S | 30 mm |
| D | 40 mm | W | 30 mm |
| G | 60 mm | | |


# Electrical connection

### Connection 1

| | |
|---|---|
| **Function** | Signal OUT |
| | Voltage supply |
| **Type of connection** | Cable |
| **Cable length** | 2,000 mm |
| **Sheathing material** | PUR |
| **Number of conductors** | 3 -wire |
| **Wire cross section** | 0.18 mm² |

| Conductor color | Conductor assignment |
|---|---|
| **Brown** | 10 ... 30 V DC |
| **Blue** | GND |
| **Black** | OUT |

# Circuit diagrams




# Operation and display

| LED | Display | Meaning |
|---|---|---|
| 1 | Green, continuous light | Ready |
| 2 | Yellow, continuous light | Switching output/switching state |

# Part number code

Part designation: **LCS-ABBBC-DDDEFF-GHHHIJJJ KK**

| | |
|---|---|
| **LCS** | **Operating principle**<br>LCS: capacitive sensor |
| **A** | **Series**<br>1: series 1 "Extended"<br>2: series 2 "Advanced" |
| **BBB** | **Design**<br>M12: series with M12 x 1 external thread<br>M18: series with M18 x 1 external thread<br>M30: series with M30 x 1.5 external thread<br>Q40: series in cubic design, length 40 mm<br>Q54: series in cubic design, length 54 mm |
| **C** | **Housing material**<br>B: Brass<br>M: metal<br>P: plastic/PBT<br>T: PTFE |
| **DDD** | **Measurement range / type of installation**<br>F03: typ. range limit 3.0 mm / embedded/flush installation<br>F04: typ. range limit 4.0 mm / embedded/flush installation<br>F05: typ. range limit 5.0 mm / embedded/flush installation<br>F06: typ. range limit 6.0 mm / embedded/flush installation<br>F08: typ. range limit 8.0 mm / embedded/flush installation<br>F10: typ. range limit 10.0 mm / embedded/flush installation<br>F15: typ. range limit 15.0 mm / embedded/flush installation<br>F20: typ. range limit 20.0 mm / embedded/flush installation<br>N06: typ. range limit 6.0 mm / non-embedded/non-flush installation<br>N08: typ. range limit 8.0 mm / non-embedded/non-flush installation<br>N10: Typ. range limit 10.0 mm / non-embedded/non-flush installation<br>N15: typ. range limit 15.0 mm / non-embedded/non-flush installation<br>N25: typ. range limit 25.0 mm / non-embedded/non-flush installation<br>N30: typ. range limit 30.0 mm / non-embedded/non-flush installation |
| **E** | **Output function**<br>B: NC and NO contact<br>N: NPN<br>P: PNP |
| **FF** | **Switching**<br>NC: Normally closed contact<br>NO: normally open contact<br>NP: programmable |
| **G** | **Connection cable**<br>K: Cable<br>n/a: no cable |

# Part number code

| | |
|---|---|
| **HHH** | **Cable length**<br>020: length 2,000 mm<br>003: length 300 mm<br>n/a: no cable |
| **I** | **Cable material**<br>P: PUR<br>T: PTFE<br>V: PVC |
| **JJJ** | **Electrical connection**<br>M08: M8 connector, 3-pin<br>M12: M12 connector, 4-pin (plug) |
| **KK** | **Special equipment**<br>L: IO-Link interface<br>T: teach-in<br>n/a: no special equipment |

**Note**

- A list with all available device types can be found on the Leuze website at www.leuze.com.

# Notes

**Observe intended use!**

- This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

**NOTE**

- The specified minimum distances have been checked with a standard switching distance. If the sensitivity of the sensor is changed using a potentiometer, this data sheet information is no longer valid.