

## Technical data sheet

### Safety sensor set

Part no.: 426672

MLC510-14-900-B






#### Contents

- Set consists of
- Technical data
- Part number code



## Set consists of

|   | Quantity | Part no. | Designation   | Article                          | Description  |
|---|----------|----------|---------------|----------------------------------|--|
|   | 2        | 429393   | BT-2HF        | Mounting bracket set             | Contains: 2x BT-HF swivel mount, 1 cylinder for mounting on the light curtain<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Clampable<br>Type of mounting device: Turning, 360°<br>Material: Metal, Plastic |
|  | 1        | 68000109 | MLC500T14-900 | Safety light curtain transmitter | Resolution: 14 mm<br>Protective field height: 900 mm<br>Operating range: 0 ... 6 m<br>Connection: Connector, M12, Metal, 5 -pin  |
|  | 1        | 68001109 | MLC510R14-900 | Safety light curtain receiver    | Function package: Basic<br>Resolution: 14 mm<br>Protective field height: 900 mm<br>Response time: 20 ms<br>Connection: Connector, M12, Metal, 5 -pin   |

## Technical data

### Basic data

|             |                                |
|-------------|--------------------------------|
| Series      | MLC 500                        |
| Device type | Set (transmitter and receiver) |
| Application | Finger protection              |

### Functions

|           |   |
|-----------|---|
| Functions | Automatic start/restart<br>Range reduction<br>Transmission channel changeover |
|-----------|---|

### Characteristic parameters

|                             |                          |
|-----------------------------|--------------------------|
| Type                        | 4, IEC/EN 61496          |
| SIL                         | 3, IEC 61508             |
| SILCL                       | 3, IEC/EN 62061          |
| Performance Level (PL)      | e, EN ISO 13849-1        |
| PFH <sub>D</sub>            | 7.73E-09 per hour        |
| Mission time T <sub>M</sub> | 20 years, EN ISO 13849-1 |
| Category                    | 4, EN ISO 13849          |

### Protective field data

|                         |           |
|-------------------------|-----------|
| Resolution              | 14 mm     |
| Protective field height | 900 mm    |
| Operating range         | 0 ... 6 m |

### Mechanical data

|            |         |
|------------|---------|
| Net weight | 2,465 g |
|------------|---------|

### Certifications

|                      |       |
|----------------------|-------|
| Degree of protection | IP 65 |
|----------------------|-------|

### Classification

|              |          |
|--------------|----------|
| ECLASS 5.1.4 | 27272704 |
| ECLASS 8.0   | 27272704 |
| ECLASS 9.0   | 27272704 |
| ECLASS 10.0  | 27272704 |
| ECLASS 11.0  | 27272704 |
| ECLASS 12.0  | 27272704 |
| ECLASS 13.0  | 27272704 |
| ECLASS 14.0  | 27272704 |
| ECLASS 15.0  | 27272704 |
| ECLASS 16.0  | 27272704 |
| ETIM 5.0     | EC002549 |
| ETIM 6.0     | EC002549 |
| ETIM 7.0     | EC002549 |
| ETIM 8.0     | EC002549 |
| ETIM 9.0     | EC002549 |
| ETIM 10.0    | EC002549 |

## Part number code

Part designation: MLCxyy-za-hhhhei-ooo

**MLC**                      **Safety light curtain**

|   |                                    |
|---|------------------------------------|
| x | Series<br>3: MLC 300<br>5: MLC 500 |
|---|------------------------------------|

## Part number code

**MLC**                      **Safety light curtain**

|             |   |
|-------------|---|
| <b>yy</b>   | <b>Function classes</b><br>00: transmitter<br>01: transmitter (AIDA)<br>02: transmitter with test input<br>10: basic receiver - automatic restart<br>11: basic receiver - automatic restart (AIDA)<br>20: standard receiver - EDM/RES selectable<br>30: Extended receiver blanking/muting or gating<br>35: Extended receiver – Gating |
| <b>z</b>    | <b>Device type</b><br>T: transmitter<br>R: receiver   |
| <b>a</b>    | <b>Resolution</b><br>14: 14 mm<br>20: 20 mm<br>30: 30 mm<br>40: 40 mm<br>90: 90 mm  |
| <b>hhhh</b> | <b>Protective field height</b><br>150 ... 3000: from 150 mm to 3000 mm  |
| <b>e</b>    | <b>Host/Guest (optional)</b><br>H: Host<br>MG: Middle Guest<br>G: Guest   |
| <b>i</b>    | <b>Interface (optional)</b><br>/A: AS-i   |
| <b>ooo</b>  | <b>Option</b><br>/V: high Vibration-proof<br>EX2: explosion protection (zones 2 + 22)<br>SPG: Smart Process Gating<br>SPG RR: Smart Process Gating – Reduced resolution   |

**Note**

|  |  |
|--|--|
|  | <p>A list with all available device types can be found on the Leuze website at <a href="http://www.leuze.com">www.leuze.com</a>.</p> |
|--|--|