

RK 3B Infrared

Retro-reflective photoelectric sensor

en 06-2012/08 50107219




**0.02
... 5.5m**



- Retro-reflective photoelectric sensors with infrared light (IR)
- High performance reserve
- Small and compact construction with robust plastic housing, protection class IP 67 for industrial application
- A²LS - Active Ambient Light Suppression
- Push-pull switching output
- High switching frequency for detection of fast events
- Special version for glossy objects, e.g. metallic surfaces

Dimensioned drawing



- A** Green indicator diode
- B** Yellow indicator diode
- C** Optical axis
- D** Potentiometer for operating range adjustment
- E** Mounting sleeve

Electrical connection

Cable, 4-wire

10-30V DC +	br/BN
OUT 2	ws/WH
GND	bl/BU
OUT 1	sw/BK



Accessories:

(available separately)

- Mounting systems (BT 3...)
- Reflectors
- Reflective tapes

We reserve the right to make changes • DS_RK3B_en_50107219.fm

Specifications

Optical data

Typ. op. range limit (TK(S) 100x100) ¹⁾	0.02 ... 5.5m
Operating range ²⁾	see tables
Light source ³⁾	LED (modulated light)
Wavelength	850nm (infrared light, not polarized)

Timing

Switching frequency	1,000Hz
Response time	0.5ms
Delay before start-up	≤ 300ms

Electrical data

Operating voltage U_B ⁴⁾	10 ... 30VDC (incl. residual ripple)
Residual ripple	≤ 15% of U_B
Open-circuit current	≤ 14mA
Switching output	.../66.1 ⁵⁾ 2 push-pull switching outputs OUT 1: PNP light switching, NPN dark switching OUT 2: PNP dark switching, NPN light switching light/dark switching
Function characteristics	≥ ($U_B - 2V$) / ≤ 2V
Signal voltage high/low	max. 100mA
Output current	adjustable with potentiometer, rotational angle approx. 250°
Operating range	

Indicators

Green LED	ready
Yellow LED	light path free

Mechanical data

Housing ⁶⁾	plastic (PC-ABS); 1 attachment sleeve, nickel-plated steel
Optics cover ⁷⁾	plastic (PMMA)
Weight	with 2m cable: 50g
Connection type	2m cable (cross section 4x0.20mm ²)


Environmental data

Ambient temp. (operation/storage)	-30°C ... +55°C / -30°C ... +70°C
Protective circuit ⁸⁾	2, 3
VDE safety class	III
Protection class	IP 67
Light source	exempt group (in acc. with EN 62471)
Standards applied	IEC 60947-5-2
Certifications	UL 508 ⁴⁾

- 1) Typ. operating range limit: max. attainable range without performance reserve
- 2) Operating range: recommended range with performance reserve
- 3) Average life expectancy 100,000h at an ambient temperature of 25°C
- 4) For UL applications: for use in class 2 circuits according to NEC only
- 5) The push-pull switching outputs must not be connected in parallel
- 6) Patent Pending Publ. No. US 7,476,848 B2
- 7) Patent Pending Publ. No. US 2009/0101791 A1
- 8) 2=polarity reversal protection, 3=short circuit protection for all transistor outputs

Remarks

Adapter plate: BT 3.2 (part no. 50103844) for alternate mounting on 25.4 mm hole spacing (Omron E3Z, Sick W100...)



Order guide

Selection table		Order code →		RK 3B/66.1 Part No. 50106852			
Equipment ↓							
Output 1 (OUT 1)	push-pull switching output	light switching	○	●			
		dark switching	●				
Output 2 (OUT 2)	push-pull switching output	light switching	○	●			
		dark switching	●				
Connection	cable 2,000mm	4-wire		●			
Configuration	potentiometer, rotational angle approx. 250°			●			

Tables



Reflectors	Operating range
1 TK(S) 100x100	0.02 ... 4.5m
4 Tape 4 50x50	0.05 ... 1.2m

1	0.02		4.5	5.5
4	0.05	1.2	1.4	

□ Operating range [m]
 □ Typ. operating range limit [m]

TK ... = adhesive
 TKS ... = screw type

Diagrams



Remarks

- **Approved purpose:**
This product may only be used by qualified personnel and must only be used for the approved purpose. This sensor is not a safety sensor and is not to be used for the protection of persons.

Mounting system:



- ① = BT 3 (part no. 50060511)
- ②+③ = BT 3.1 ¹⁾ (part no. 50105585)
- ①+②+③ = BT 3B (part no. 50105546)

1) Packaging unit: PU = 10 pcs.