

# **Technical data sheet** Diffuse sensor with background suppression

Part no.: 50139641

HT25CL1/2N



#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Part number code
- Notes
- Further information
- Accessories

















For Illustration purposes only

### **Technical data**



#### Basic data

Series	25C
Operating principle	Diffuse reflection principle with background suppression

Optical data	
Black-white error	< 10% up to 250 mm
Operating range	Guaranteed operating range
Operating range, white 90%	0.005 0.6 m
Operating range, gray 18%	0.015 0.45 m
Operating range, black 6%	0.02 0.3 m
Operating range limit	0.005 0.6 m
Operating range limit	Typical operating range
Adjustment range	50 600 mm
Beam path	Collimated
Light source	Laser, Red
Wavelength	650 nm
Laser class	1, IEC/EN 60825-1:2014
Max. laser power	0.0043 W
Transmitted-signal shape	Pulsed
Pulse duration	4.5 µs
Light spot size [at sensor distance]	3 mm x 5 mm [1,000 mm]
Type of light spot geometry	elliptic
Shift angle	Typ. ± 1.5°

#### **Electrical data**

Protective circuit	Polarity reversal protection
	Short circuit protected

#### Performance data

Supply voltage U <sub>B</sub>	10 30 V, DC, Incl. residual ripple
Residual ripple	0 15 %, From U <sub>B</sub>
Open-circuit current	0 20 mA

#### Outputs

Number of digital switching outputs 2 Piece(s)

#### **Switching outputs**

Voltage type	DC
Switching current, max.	100 mA
Switching voltage	high: ≥(U <sub>B</sub> -2.5V)
	low: ≤ 2.5 V

### Switching output 1

Switching element	Transistor, NPN
Switching principle	Light switching

#### Switching output 2

Switching element	Transistor, NPN
Switching principle	Dark switching

#### Time behavior

Switching frequency	2,500 Hz	
Response time	0.2 ms	
Readiness delay	300 ms	

Connection i	
Function	Signal OUT
	Voltage supply
Type of connection	Cable
Cable length	2,000 mm
Sheathing material	PUR

Cable color Black **Number of conductors** 4 -wire 0.2 mm<sup>2</sup> Wire cross section

#### **Mechanical data**

Connection 1

Dimension (W x H x L)	15 mm x 42.7 mm x 30 mm
Housing material	Plastic
Plastic housing	ABS
Lens cover material	Plastic
Net weight	55 g
Housing color	Red
Type of fastening	Through-hole mounting with M4 thread
	Via optional mounting device
Compatibility of materials	ECOLAB

#### **Operation and display**

Type of display	LED
Number of LEDs	2 Piece(s)
Operational controls	Multiturn potentiometer
Function of the operational control	Range adjustment

#### **Environmental data**

Ambient temperature, operation	-40 60 °C
Ambient temperature, storage	-40 70 °C

#### Certifications

Degree of protection	IP 67
	IP 69K
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2


#### Classification

Customs tariff number	85365019
ECLASS 5.1.4	27270904
ECLASS 8.0	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ECLASS 13.0	27270903
ECLASS 14.0	27270903
ECLASS 15.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
ETIM 9.0	EC002719
ETIM 10.0	EC002719

# **Dimensioned drawings**

Leuze

All dimensions in millimeters



- Green LED
- Yellow LED
- Optical axis
- C1 Receiver
- C2 Transmitter
- D Range adjustment

# **Electrical connection**

#### **Connection 1**

Function	Signal OUT Voltage supply
Type of connection	Cable
Cable length	2,000 mm
Sheathing material	PUR
Cable color	Black
Number of conductors	4 -wire
Wire cross section	0.2 mm <sup>2</sup>


#### **Conductor color Conductor assignment**

Brown	V+
White	OUT 2
Blue	GND
Black	OUT 1


# **Diagrams**




Typ. response behavior (focusing distance 250 mm)




- Distance [mm]
- Misalignment [mm]



Typ. response behavior (focusing distance 600 mm)




- Distance [mm]
- Misalignment [mm]




# **Diagrams**



# Typ. black/white behavior



- Range [mm]
- Reduction of range [mm]
- White 90%
- Gray 18%
- Black 6%



# **Operation and display**

LED	Display	Meaning
1	Green, continuous light	Operational readiness
2	Yellow, continuous light	Object detected

# Part number code

Part designation: AAA25C d EE-f.GGH/iJ-K

AAA25C	Operating principle / construction HT25C: Diffuse reflection sensor with background suppression PRK25C: Retro-reflective photoelectric sensor with polarization filter LS25C: Throughbeam photoelectric sensor transmitter LE25C: Throughbeam photoelectric sensor receiver DRT25C: Dynamic reference diffuse sensor
d	Light type n/a: red light l: infrared light
EE	Light source n/a: LED PP: Power PinPoint LED L1: laser class 1 L2: laser class 2
f	Preset range (optional) n/a: operating range acc. to data sheet xxxF: Preset range [mm]
GG	Equipment A: Autocollimation principle (single lens) S: small light spot D: Detection of stretch-wrapped objects X: extended model HF: Suppression of HF illumination (LED) XL: Extra long light spot T: autocollimation principle (single lens) for highly transparent bottles without tracking TT: autocollimation principle (single lens) for highly transparent bottles with tracking F: Foreground suppression R: greater operating range SL: Slit diaphragm

### Part number code



Н	Operating range adjustment  1: 270° potentiometer  2: multiturn potentiometer  3: teach-in via button  R: greater operating range
i	Switching output/function OUT 1/IN: Pin 4 or black conductor  2: NPN transistor output, light switching N: NPN transistor output, dark switching 4: PNP transistor output, light switching P: PNP transistor output, dark switching X: pin not used 8: activation input (activation with high signal) L: IO-Link interface (SIO mode: PNP light switching, NPN dark switching) 6: push-pull switching output, PNP light switching, NPN dark switching G: Push-pull switching output, PNP dark switching, NPN light switching
J	Switching output / function OUT 2/IN: pin 2 or white conductor  2: NPN transistor output, light switching N: NPN transistor output, dark switching 4: PNP transistor output, light switching P: PNP transistor output, dark switching W: warning output X: pin not used 6: push-pull switching output, PNP light switching, NPN dark switching T: teach-in via cable G: Push-pull switching output, PNP dark switching, NPN light switching 8: activation input (activation with high signal)
К	Electrical connection n/a: cable, standard length 2000 mm, 4-wire 200-M12: cable, length 200 mm with M12 connector, 4-pin, axial (plug) M8: M8 connector, 4-pin (plug) M12: M12 connector, 4-pin (plug) 200-M8: cable, length 200 mm with M8 connector, 4-pin, axial (plug) M8.1: Snap-in, M8 connector, 4-pin (plug)

#### Note



 $\ ^{\mbox{\tiny $b$}}\ \mbox{A list with all available device types can be found on the Leuze website at www.leuze.com.}$ 

#### **Notes**



#### Observe intended use!



- \$ This product is not a safety sensor and is not intended as personnel protection.
- \$ The product may only be put into operation by competent persons.
- b Only use the product in accordance with its intended use.



#### **WARNING! LASER RADIATION - CLASS 1 LASER PRODUCT**



The device satisfies the requirements of IEC/EN 60825-1:2014 safety regulations for a product of laser class 1 and complies with 21 CFR 1040.10 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019.

- b Observe the applicable statutory and local laser protection regulations.
- The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device. Repairs must only be performed by Leuze electronic GmbH + Co. KG.

We reserve the right to make technical changes

# **Further information**



- Light source: Average life expectancy 50,000 h at an ambient temperature of 25  $^{\circ}\text{C}$
- · Sum of the output currents for both outputs 100 mA

### **Accessories**

# Mounting technology - Mounting brackets

	Part no.	Designation	Article	Description
( t	50118543	BT 300M.5	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type, Suited for M4 screws Type of mounting device: Adjustable Material: Stainless steel

# Mounting technology - Rod mounts

	Part no.	Designation	Article	Description
To be	50117829	BTP 200M-D12	Mounting system	Design of mounting device: Protection hood Fastening, at system: For 12 mm rod Mounting bracket, at device: Screw type Type of mounting device: Clampable, Adjustable, Turning, 360° Material: Metal
	50117252	BTU 300M-D12	Mounting system	Design of mounting device: Mounting system Fastening, at system: For 12 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type, Suited for M4 screws Type of mounting device: Clampable, Adjustable, Turning, 360° Material: Metal

#### Note



🔖 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.