

Technical data sheet Reflector

Part no.: 50104131

MTKS 40x60.1

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Mechanical data	
Design	Rectangular
Triple reflector size	1.2 mm
Mounting dimension, width	41 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	7.5 mm
Reflective surface, height	56 mm
Reflective surface, width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Mikrotriple
Net weight	1.2 g
Type of fastening	Adhesive
	Through-hole mounting

Classification	
Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Environmental data	
Ambient temperature, operation	-40 ... 65 °C
Certifications	
Degree of protection	IP 67

Dimensioned drawings

All dimensions in millimeters

