

Technical data sheet

Y distribution box

Part no.: 50135996

YV U-SDD-25-83-83-X04

Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Accessories



For illustration purposes only



Technical data

Connection

Number of connections 3 Piece(s)

Connection 1

Type of connection Connector
Thread size M8
Type Female
No. of pins 3 -pin
Encoding A-coded
Version Axial

Connection 2

Type of connection Connector
Thread size M8
Type Female
No. of pins 3 -pin
Encoding A-coded
Version Axial

Connection 3

Type of connection Connector
Thread size M12
Type Male
No. of pins 5 -pin
Encoding A-coded
Version Axial

Cable properties

Shielded No

Mechanical data

Design Cubic
Dimension (W x H x L) 33.5 mm x 15.8 mm x 40.4 mm
Width across flats 13 mm
Net weight 16 g
Material PUR

Environmental data

Ambient temperature, operation -25 ... 85 °C

Certifications


Degree of protection IP 67

Classification

Customs tariff number 85366990
ECLASS 5.1.4 27279201
ECLASS 8.0 27440104
ECLASS 9.0 27069190
ECLASS 10.0 27440111
ECLASS 11.0 27440111
ECLASS 12.0 27440111
ECLASS 13.0 27440111
ECLASS 14.0 27440111
ECLASS 15.0 27440111
ECLASS 16.0 27440111
ETIM 5.0 EC002498
ETIM 6.0 EC002925
ETIM 7.0 EC002925
ETIM 8.0 EC003558
ETIM 9.0 EC003558
ETIM 10.0 EC003558


Dimensioned drawings

All dimensions in millimeters



Dimensioned drawings

Circuit diagram



- a Connection 3, M12 connector
- b Connection 1, M8 socket
- c Connection 2, M8 socket

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M8
Type	Female
No. of pins	3 -pin
Encoding	A-coded
Version	Axial

Connection 2

Type of connection	Connector
Thread size	M8
Type	Female
No. of pins	3 -pin
Encoding	A-coded
Version	Axial

Connection 3

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Version	Axial

Accessories

General

	Part no.	Designation	Article	Description
	50132266	TT-Set 0,6-13	Tool	Type: Torque key Width across flats: 13 mm Torque: 0.6 N·m Material: Plastic, Stainless steel Ambient temperature: -40 ... 120 °C

Note	
	A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.