

Technical data sheet Reflector

Part no.: 50106957

TKS 40x60.P

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only



Technical data

Basic data

Area of application	Pharmaceutical
---------------------	----------------

Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	41 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	8 mm
Reflective surface, height	56 mm
Reflective surface, width	37 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PES
Structure, active surface	Triple
Net weight	16 g
Type of fastening	Adhesive
	Through-hole mounting
Compatibility of materials	ECOLAB

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

