

## Technical data sheet

### Distance diffuse sensor with background suppression

Part no.: 50153162

ODT3CL1-2M.3/L6-1000-M12

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Part number code
- Notes
- Further information
- Accessories



For illustration purposes only



CDRH

IO-Link



## Technical data

### Basic data

|                     |                                                     |
|---------------------|-----------------------------------------------------|
| Series              | 3C                                                  |
| Operating principle | Distance diffuse sensor with background suppression |

### Special version

|                 |                                                             |
|-----------------|-------------------------------------------------------------|
| Special version | 2 independent switching outputs<br>Measurement value output |
|-----------------|-------------------------------------------------------------|

### Optical data

|                             |                                                |
|-----------------------------|------------------------------------------------|
| Black-white error           | ±20 mm                                         |
| Operating range             | 0.07 ... 2 m                                   |
| Adjustment range            | 50 ... 2,500 mm                                |
| Beam path                   | Focused                                        |
| Light source                | Laser, Red                                     |
| Wavelength                  | 680 nm                                         |
| Laser class                 | 1, IEC 60825-1:2014 / EN 60825-1:2014+A11:2021 |
| Transmitted-signal shape    | Pulsed                                         |
| Type of light spot geometry | Round                                          |
| Shift angle                 | Typ. ± 1.5°                                    |

### Measurement data

|                                        |                 |
|----------------------------------------|-----------------|
| Measurement range                      | 50 ... 2,500 mm |
| Resolution                             | 1.0 mm          |
| Accuracy                               | -20 ... 20 mm   |
| Reproducibility (1 sigma)              | 0 ... 8 mm      |
| Measurement value output               | via IO-Link     |
| Optical distance measurement principle | Time of flight  |

### Electrical data

|                    |                                                                                 |
|--------------------|---------------------------------------------------------------------------------|
| Protective circuit | Polarity reversal protection<br>Short circuit protected<br>Transient protection |
|--------------------|---------------------------------------------------------------------------------|

### Performance data

|                      |                                        |
|----------------------|----------------------------------------|
| Supply voltage $U_B$ | 10 ... 30 V, DC, Incl. residual ripple |
| Residual ripple      | 0 ... 15 %, From $U_B$                 |
| Open-circuit current | 0 ... 35 mA                            |

### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 2 Piece(s) |
|-------------------------------------|------------|

### Switching outputs

|                         |                                           |
|-------------------------|-------------------------------------------|
| Type                    | Digital switching output                  |
| Voltage type            | DC                                        |
| Switching current, max. | 90 mA                                     |
| Switching voltage       | high: $\geq(U_B - 2V)$<br>low: $\leq 2 V$ |

### Switching output 1

|                     |                                                      |
|---------------------|------------------------------------------------------|
| Assignment          | Connection 1, pin 4                                  |
| Switching element   | Transistor, Push-pull                                |
| Switching principle | IO-Link / light switching (PNP)/dark switching (NPN) |

### Switching output 2

|                     |                                            |
|---------------------|--------------------------------------------|
| Assignment          | Connection 1, pin 2                        |
| Switching element   | Transistor, Push-pull                      |
| Switching principle | Light switching (PNP)/dark switching (NPN) |

### Time behavior

|                     |                                                |
|---------------------|------------------------------------------------|
| Switching frequency | 7 ... 15 Hz, depending on diffuse reflectance  |
| Response time       | 33 ... 70 ms, depending on diffuse reflectance |
| Readiness delay     | 300 ms                                         |

### Interface

|                  |                      |
|------------------|----------------------|
| Type             | IO-Link              |
| IO-Link          |                      |
| COM mode         | COM3                 |
| Profile          | Smart sensor profile |
| Min. cycle time  | COM3 = 0.6 ms        |
| Frame type       | 2.V                  |
| Specification    | V1.1                 |
| Device ID        | 2220                 |
| SIO-mode support | Yes                  |

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

### Connection 1

|                      |                                           |
|----------------------|-------------------------------------------|
| Function             | Signal IN<br>Signal OUT<br>Voltage supply |
| Type of connection   | Cable with connector                      |
| Cable length         | 1,000 mm                                  |
| Sheathing material   | PUR                                       |
| Cable color          | Black                                     |
| Number of conductors | 4 -wire                                   |
| Wire cross section   | 0.2 mm <sup>2</sup>                       |
| Thread size          | M12                                       |
| Type                 | Male                                      |
| Material             | Metal                                     |
| No. of pins          | 4 -pin                                    |
| Encoding             | A-coded                                   |

### Mechanical data

|                            |                                                       |
|----------------------------|-------------------------------------------------------|
| Design                     | Cubic                                                 |
| Dimension (W x H x L)      | 11.4 mm x 34.2 mm x 18.3 mm                           |
| Housing material           | Plastic                                               |
| Plastic housing            | PC-ABS                                                |
| Lens cover material        | Plastic / PMMA                                        |
| Net weight                 | 30 g                                                  |
| Housing color              | Red                                                   |
| Type of fastening          | Through-hole mounting<br>Via optional mounting device |
| Compatibility of materials | ECOLAB                                                |

### Operation and display

|                                     |                                          |
|-------------------------------------|------------------------------------------|
| Type of display                     | LED                                      |
| Number of LEDs                      | 2 Piece(s)                               |
| Operational controls                | Teach button                             |
| Function of the operational control | Light/dark switching<br>Range adjustment |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -30 ... 50 °C |
| Ambient temperature, storage   | -40 ... 70 °C |

## Technical data

### Certifications


|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
|                      | IP 69K        |
| Protection class     | III           |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270904 |
| ECLASS 8.0            | 27270904 |
| ECLASS 9.0            | 27270904 |
| ECLASS 10.0           | 27270904 |
| ECLASS 11.0           | 27270904 |
| ECLASS 12.0           | 27270903 |
| ECLASS 13.0           | 27270903 |
| ECLASS 14.0           | 27270903 |
| ECLASS 15.0           | 27270903 |
| ETIM 5.0              | EC002719 |
| ETIM 6.0              | EC002719 |
| ETIM 7.0              | EC002719 |
| ETIM 8.0              | EC002719 |
| ETIM 9.0              | EC002719 |
| ETIM 10.0             | EC002719 |

Dimensioned drawings

All dimensions in millimeters



Electrical connection

Connection 1

|                      |                      |
|----------------------|----------------------|
| Function             | Signal IN            |
|                      | Signal OUT           |
|                      | Voltage supply       |
| Type of connection   | Cable with connector |
| Cable length         | 1,000 mm             |
| Sheathing material   | PUR                  |
| Cable color          | Black                |
| Number of conductors | 4 -wire              |
| Wire cross section   | 0.2 mm²              |
| Thread size          | M12                  |
| Type                 | Male                 |
| Material             | Metal                |
| No. of pins          | 4 -pin               |
| Encoding             | A-coded              |


Electrical connection

| Pin | Pin assignment  |
|-----|-----------------|
| 1   | V+              |
| 2   | OUT 2           |
| 3   | GND             |
| 4   | IO-Link / OUT 1 |




Diagrams

Typ. response behavior (white 90 %)



Typ. black/white behavior / measurement accuracy



Operation and display

| LED | Display                  | Meaning         |
|-----|--------------------------|-----------------|
| 1   | Green, continuous light  | Ready           |
| 2   | Yellow, continuous light | Object detected |

## Part number code

Part designation: **AAA 3C d EE-f.GG H/i J-K**

|              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>AAA3C</b> | <b>Operating principle / construction</b><br>HT3C: Diffuse reflection sensor with background suppression<br>LS3C: Throughbeam photoelectric sensor transmitter<br>LE3C: Throughbeam photoelectric sensor receiver<br>PRK3C: Retro-reflective photoelectric sensor with polarization filter<br>ODT3C: Distance diffuse sensor with background suppression                                                                                                                                                                                                                                                                   |
| <b>d</b>     | <b>Light type</b><br>n/a: red light<br>I: infrared light                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>EE</b>    | <b>Light source</b><br>n/a: LED<br>L1: laser class 1<br>L2: laser class 2<br>PP: Power PinPoint® LED                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>f</b>     | <b>Preset range (optional)</b><br>n/a: operating range acc. to data sheet<br>xxxF: Preset range [mm]<br>2M: operating range of 2 meters                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| <b>GG</b>    | <b>Equipment</b><br>n/a: standard<br>A: Autocollimation principle (single lens) for positioning tasks<br>B: Housing model with two M3 threaded sleeves, brass<br>F: Permanently set range<br>L: Long light spot<br>S: small light spot<br>T: autocollimation principle (single lens) for highly transparent bottles without tracking<br>TT: autocollimation principle (single lens) for highly transparent bottles with tracking<br>V: V-optics<br>XL: Extra long light spot<br>X: extended model<br>HF: Suppression of HF illumination (LED)                                                                              |
| <b>H</b>     | <b>Operating range adjustment</b><br>n/a with HT: range adjustable via 8-turn potentiometer<br>n/a with retro-reflective photoelectric sensors (PRK): operating range not adjustable<br>1: 270° potentiometer<br>3: teach-in via button<br>6: auto-teach                                                                                                                                                                                                                                                                                                                                                                   |
| <b>i</b>     | <b>Switching output/function OUT 1/IN: Pin 4 or black conductor</b><br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>6: push-pull switching output, PNP light switching, NPN dark switching<br>G: Push-pull switching output, PNP dark switching, NPN light switching<br>L: IO-Link interface (SIO mode: PNP light switching, NPN dark switching)<br>8: activation input (activation with high signal)<br>X: pin not used<br>1: IO-Link / light switching (NPN) / dark switching (PNP) |
| <b>J</b>     | <b>Switching output / function OUT 2/IN: pin 2 or white conductor</b><br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>6: push-pull switching output, PNP light switching, NPN dark switching<br>G: Push-pull switching output, PNP dark switching, NPN light switching<br>W: warning output<br>X: pin not used<br>8: activation input (activation with high signal)<br>9: deactivation input (deactivation with high signal)<br>T: teach-in via cable                                 |

## Part number code

|   |                                                                       |
|---|-----------------------------------------------------------------------|
| K | <b>Electrical connection</b>                                          |
|   | n/a: cable, standard length 2000 mm, 4-wire                           |
|   | 5000: cable, standard length 5000 mm, 4-wire                          |
|   | M8: M8 connector, 4-pin (plug)                                        |
|   | M8.3: M8 connector, 3-pin (plug)                                      |
|   | 200-M8: cable, length 200 mm with M8 connector, 4-pin, axial (plug)   |
|   | 200-M8.3: cable, length 200 mm with M8 connector, 3-pin, axial (plug) |
|   | 200-M12: cable, length 200 mm with M12 connector, 4-pin, axial (plug) |

### Note



A list with all available device types can be found on the Leuze website at [www.leuze.com](http://www.leuze.com).

## Notes



### Observe intended use!



- ⚡ This product is not a safety sensor and is not intended as personnel protection.
- ⚡ The product may only be put into operation by competent persons.
- ⚡ Only use the product in accordance with its intended use.

### For UL applications:



- ⚡ For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- ⚡ These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)



### ATTENTION! LASER RADIATION – CLASS 1 LASER PRODUCT



- The device satisfies the requirements of IEC 60825-1:2014 / EN 60825-1:2014+A11:2021 safety regulations for a product of **laser class 1** and complies with 21 CFR 1040.10 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019.
- ⚡ Observe the applicable statutory and local laser protection regulations.
  - ⚡ The device must not be tampered with and must not be changed in any way.
    - There are no user-serviceable parts inside the device.
    - There are no user-serviceable parts inside the device.
    - Repairs must only be performed by Leuze electronic GmbH + Co. KG.

## Further information

- Sum of the output currents for both outputs, 50 mA for ambient temperatures > 40 °C
- With a supply voltage >18 V and an ambient temperature <40 °C, the maximum switching current is 100 mA per switching output.
- When starting the sensor below -20 °C, a warmup time of one minute is required until the first teach-in

## Accessories

### Connection technology - Connection cables

|                                                                                   | Part no. | Designation       | Article          | Description                                                                                                                                                              |
|-----------------------------------------------------------------------------------|----------|-------------------|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50130850 | KD U-M8-4A-V1-050 | Connection cable | Connection 1: Connector, M8, Axial, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5.000 mm<br>Sheathing material: PVC  |
|                                                                                   | 50130871 | KD U-M8-4W-V1-050 | Connection cable | Connection 1: Connector, M8, Angled, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5.000 mm<br>Sheathing material: PVC |

### Mounting technology - Mounting brackets

|                                                                                    | Part no. | Designation | Article         | Description                                                                                                                                                                              |
|------------------------------------------------------------------------------------|----------|-------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50060511 | BT 3        | Mounting device | Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Rigid<br>Material: Metal |

### Mounting technology - Rod mounts

|                                                                                     | Part no. | Designation  | Article         | Description                                                                                                                                                                                                                                                  |
|-------------------------------------------------------------------------------------|----------|--------------|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50117255 | BTU 200M-D12 | Mounting system | Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod, Sheet-metal mounting<br>Mounting bracket, at device: Screw type, Suited for M3 screws<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal |

#### Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.