

## Technical data sheet

### Connection unit

Part no.: 50030838

MA 31 130

#### Contents

- Technical data
- Electrical connection
- Operation and display



Figure can vary



# Technical data

## Basic data

Series	MA 31
--------	-------

## Electrical data

Protective circuit	Overvoltage protection
--------------------	------------------------

### Performance data

Supply voltage $U_B$	18 ... 36 V, DC
----------------------	-----------------

## Interface

Type	RS 422, RS 485
------	----------------

## Connection

Number of connections	1 Piece(s)
-----------------------	------------

### Connection 1

Function	Connection to device Data interface Voltage supply
----------	--

Type of connection	Terminal
--------------------	----------

No. of pins	25 -pin
-------------	---------

### Connection 2

Function	Service interface
----------	-------------------

Type of connection	Sub-D
--------------------	-------

No. of pins	9 -pin
-------------	--------

## Mechanical data

Design	Cubic
--------	-------

Dimension (W x H x L)	120 mm x 55 mm x 180 mm
-----------------------	-------------------------

Housing material	Metal
------------------	-------

Net weight	640 g
------------	-------

Housing color	Red, RAL 3000
---------------	---------------

Type of fastening	Through-hole mounting
-------------------	-----------------------

## Operation and display

Type of display	LED
-----------------	-----

Number of LEDs	6 Piece(s)
----------------	------------

## Environmental data

Ambient temperature, operation	0 ... 50 °C
--------------------------------	-------------

Ambient temperature, storage	-20 ... 60 °C
------------------------------	---------------

Relative humidity (non-condensing)	5 ... 90 %
------------------------------------	------------

## Certifications

Degree of protection	IP 65
----------------------	-------

## Classification

Customs tariff number	84733080
-----------------------	----------

ECLASS 5.1.4	27069190
--------------	----------

ECLASS 8.0	27069190
------------	----------

ECLASS 9.0	27069190
------------	----------

ECLASS 10.0	27069190
-------------	----------

ECLASS 11.0	27069090
-------------	----------

ECLASS 12.0	27069090
-------------	----------

ETIM 5.0	EC001855
----------	----------

ETIM 6.0	EC001855
----------	----------

ETIM 7.0	EC001855
----------	----------

# Electrical connection

## Connection 1

Function	Connection to device Data interface Voltage supply
----------	--

Type of connection	Terminal
--------------------	----------

Cable gland	PG9
-------------	-----

No. of pins	25 -pin
-------------	---------

## Terminal

## Assignment

1	TxD+
---	------

2	TxD-
---	------

3	RxD+
---	------

4	RxD-
---	------

5	Res.
---	------

6	GND
---	-----

7	n.c.
---	------

8	n.c.
---	------

9	n.c.
---	------

10	n.c.
----	------

11	n.c.
----	------

## Electrical connection

Terminal	Assignment
12	n.c.
13	n.c.
14	n.c.
15	n.c.
16	n.c.
17	V_IN
18	V_IN
19	GNDIN
20	GNDIN
21	PE
22	n.c.
23	RS 485 A
24	RS 485 B
25	RS 485 GND
26	
27	

### Connection 2

Function	Service interface
Type of connection	Sub-D
Type	Male
No. of pins	9 -pin

Pin	Pin assignment
1	n.c.
2	RxD Service
3	TXD service
4	n.c.
5	RS 232 GND
6	n.c.
7	n.c.
8	n.c.
9	n.c.

## Operation and display

LED	Display	Meaning
1	Green, continuous light	BUS OK
	Green, flashing	Bus error
2	Green, flashing	Data transmission active
	Off	None.
3	Green, continuous light	Operational readiness
	Green, flashing	Device ok, initialization phase
4	Yellow, flashing	None.
	Yellow, continuous light	Device error
5	Red, continuous light	Trigger
	Off	None.
6	Green, flashing	Switching output/switching state
	Off	None.