

## Technical data sheet

### Connection cable

Part no.: 50106152

K-D M8A-4P-2m-FAB

#### Contents

- Technical data
- Electrical connection
- Circuit diagrams




Figure can vary



# Technical data

## Electrical data

### Performance data

Operating voltage Max. 30 V AC/DC

## Connection

### Connection 1

Type of connection	Connector
Thread size	M8
Type	Female
Handle body material	PUR
No. of pins	4 -pin
Version	Axial
Connector, LED	No
Lock	Screw fitting, stainless steel V4A, recommended torque 0.6 Nm, self-locking

### Connection 2

Type of connection Open end

### Cable properties

Number of conductors	4 Piece(s)
Wire cross section	0.4444 mm <sup>2</sup>
AWG	24
Sheathing color	Black
Shielded	No
Silicone-free	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	4.7 mm
Cable length	2,000 mm
Sheathing material	PVC
Wire insulation	PVC
Suitability for drag chains	No
Properties of the outer sheathing	Free of CFC, cadmium, silicone and lead, easily machine-processable
Resistance of the outer sheathing	Good oil, gasoline and chemical resistance, flame retardant in accordance with UL 1581 VW1 / CSA FT1

## Mechanical data

Bending radius, flexible laying, min. Min. 10 x cable diameter

Bending radius, stationary laying, min. Min. 5 x cable diameter

## Operation and display

## Environmental data

Ambient temperature, operation, flexible use -5 ... 80 °C

Ambient temperature, operation, stationary use -30 ... 80 °C

## Certifications

Degree of protection IP 65

IP 67

IP 69K

Certifications c UL US

UL

## Classification

Customs tariff number 85444290

ECLASS 5.1.4 27279201

ECLASS 8.0 27279218

ECLASS 9.0 27060311

ECLASS 10.0 27060311

ECLASS 11.0 27060311

ECLASS 12.0 27060311

ETIM 5.0 EC001855

ETIM 6.0 EC001855

ETIM 7.0 EC001855

# Electrical connection


## Connection 1

Type of connection	Connector
Thread size	M8
Type	Female
Handle body material	PUR
No. of pins	4 -pin
Version	Axial
Connector, LED	No
Lock	Screw fitting, stainless steel V4A, recommended torque 0.6 Nm, self-locking

## Pin

1	Brown
2	White
3	Blue
4	Black

## Conductor color



## Electrical connection

### Connection 2

Type of connection

Open end

## Circuit diagrams

### Wiring schematic

