

## Technical data sheet

### Connection cable

Part no.: 50135136

KD S-M12-8W-P1-250

#### Contents

- Technical data
- Electrical connection
- Circuit diagrams




Figure can vary



## Technical data

### Electrical data

#### Performance data

Operating voltage 30 V AC/DC

### Connection

#### Connection 1

|                      |  |
|----------------------|--|
| Type of connection   | Connector  |
| Thread size          | M12  |
| Type                 | Female   |
| Handle body material | PUR  |
| No. of pins          | 8 -pin   |
| Encoding             | A-coded  |
| Version              | Angled   |
| Connector, LED       | No   |
| Lock                 | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

#### Connection 2

Type of connection Open end

#### Cable properties

|                                   |   |
|-----------------------------------|---|
| Number of conductors              | 8 Piece(s)  |
| Wire cross section                | 0.25 mm <sup>2</sup>  |
| AWG                               | 24  |
| Sheathing color                   | Black   |
| Shielded                          | Yes   |
| Silicone-free                     | Yes   |
| Cable design                      | Connection cable (open on one end)  |
| Cable diameter (external)         | 6.6 mm  |
| Cable length                      | 25,000 mm   |
| Sheathing material                | PUR   |
| Wire insulation                   | PP  |
| Traverse rate                     | Max. 3.3 m/s with horiz. traverse path of 5m and max. acceleration of 5m/s <sup>2</sup>   |
| Suitability for drag chains       | Yes   |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable  |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |
| Torsion suitability               | ±30° / m (max. 2 mio. cycles with 35 cycles / min)  |

### Mechanical data

|   |                          |
|---|--------------------------|
| Width across flats                      | 13 mm                    |
| Bending cycles                          | 2,000,000 Piece(s)       |
| Bending radius, flexible laying, min.   | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 10 x cable diameter |

### Operation and display

#### Environmental data

|  |               |
|--|---------------|
| Ambient temperature, operation, flexible use   | -20 ... 80 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

#### Certifications

|                      |       |
|----------------------|-------|
| Degree of protection | IP 65 |
|                      | IP 67 |

#### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |

## Electrical connection

### Connection 1


|                      |           |
|----------------------|-----------|
| Type of connection   | Connector |
| Thread size          | M12       |
| Type                 | Female    |
| Handle body material | PUR       |

# Electrical connection

## Connection 1

|                |  |
|----------------|--|
| No. of pins    | 8 -pin   |
| Encoding       | A-coded  |
| Version        | Angled   |
| Connector, LED | No   |
| Lock           | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

| Pin | Conductor color |
|-----|-----------------|
| 1   | White           |
| 2   | Brown           |
| 3   | Green           |
| 4   | Yellow          |
| 5   | Gray            |
| 6   | Pink            |
| 7   | Blue            |
| 8   | Red             |



## Connection 2

|                    |          |
|--------------------|----------|
| Type of connection | Open end |
|--------------------|----------|

# Circuit diagrams

## Wiring schematic

