

## Technical data sheet

### Reflector

Part no.: 50003192

TK 100x100

#### Contents

- Technical data
- Dimensioned drawings



Figure can vary

## Technical data

### Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	99.4 mm
Mounting dimension, height	99.4 mm
Mounting dimension, thickness	8.7 mm
Reflection surface height	96 mm
Reflection surface width	96 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	61 g
Type of fastening	Rear side can be glued

### Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

