

## Technical data sheet

### Contour measurement system

Part no.: 50143561

CMS748i-ENC1-0640-0640

#### Contents



- Set consists of
- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Notes
- Accessories



For illustration purposes only



## Set consists of

|                                                                                     | Quantity | Part no. | Designation                 | Article                   | Description                                                                                                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------|----------|----------|-----------------------------|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|     | 2        | 424417   | BT-2P40                     | Mounting bracket set      | Contains: BT-P40 clamp bracket, 2x<br>Bore hole 1: M6<br>Bore hole 2: M6<br>Design of mounting device: Mounting clamp<br>Fastening, at system: Groove mounting<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Clampable, Suitable for mounting in UDC-S2, DC-S2 device columns<br>Material: Metal |
|                                                                                     | 2        | 50118744 | CML730i-R05-640.A/L-M12     | Light curtain receiver    | Interface: IO-Link<br>Connection: Connector, M12, Axial, 8 -pin                                                                                                                                                                                                                                                                |
|    | 2        | 50118583 | CML730i-T05-640.A-M12       | Light curtain transmitter | Operating range: 0.1 ... 4 m<br>Connection: Connector, M12, Axial, 5 -pin                                                                                                                                                                                                                                                      |
|    | 2        | 50129781 | KDS DN-M12-5A-M12-5A-P3-050 | Interconnection cable     | Application: Oil and lubricant resistant<br>Suitable for interface: DeviceNet, CANopen<br>Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin<br>Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin<br>Shielded: Yes<br>Cable length: 5,000 mm<br>Sheathing material: PUR                                     |
|   | 3        | 50135146 | KDS S-M12-8A-M12-8A-P1-050  | Interconnection cable     | Application: Oil and lubricant resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 8 -pin<br>Connection 2: Connector, M12, Axial, Male, A-coded, 8 -pin<br>Shielded: Yes<br>Cable length: 5,000 mm<br>Sheathing material: PUR                                                                                   |
|  | 1        | 50144568 | LMSMA35500024KH 10M16       | Rotary encoder            |                                                                                                                                                                                                                                                                                                                                |
|  | 1        | 50142931 | LSC748-ENC-100              | Switch cabinet            | Supply voltage: 100 ... 263 V, AC<br>Switching inputs: 4 Piece(s)<br>Switching outputs: 4 Piece(s)<br>Connections: 13 Piece(s)                                                                                                                                                                                                 |
|   |          |          |                             |                           |                                                                                                                                                                                                                                                                                                                                |

|             |                                       |
|-------------|---------------------------------------|
| Series      | CMS 7xxi                              |
| Contains    | 1x dongle CMS700<br>1x rotary encoder |
| Order guide | Additional models on request          |

### Functions

|           |                                         |
|-----------|-----------------------------------------|
| Functions | For a minimum object height $\geq 5$ mm |
|-----------|-----------------------------------------|

## Technical data

### Optical data

|                                    |                |
|------------------------------------|----------------|
| Operating range                    | 0.1 ... 4.5 m  |
| Operating range, transparent media | 0.1 ... 1.75 m |
| Operating range limit              | 0.1 ... 6 m    |
| Measurement field length 1         | 640 mm         |
| Measurement field length 2         | 640 mm         |
| Beam spacing                       | 5 mm           |

### Electrical data

|                                                      |                                                                                 |
|------------------------------------------------------|---------------------------------------------------------------------------------|
| Protective circuit                                   | Polarity reversal protection<br>Short circuit protected<br>Transient protection |
| Output current, continuous current per channel, max. | 100 mA                                                                          |

### Performance data

|                      |               |
|----------------------|---------------|
| Supply voltage $U_B$ | 100 ... 263 V |
| Open-circuit current | 250 mA        |

### Inputs

|                                    |            |
|------------------------------------|------------|
| Number of digital switching inputs | 4 Piece(s) |
|------------------------------------|------------|

### Switching inputs

|                   |                         |
|-------------------|-------------------------|
| Type              | Digital switching input |
| Voltage type      | DC                      |
| Switching voltage | 24 V, VIN               |

### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 4 Piece(s) |
|-------------------------------------|------------|

### Switching outputs

|                   |                          |
|-------------------|--------------------------|
| Type              | Digital switching output |
| Voltage type      | AC                       |
| Switching voltage | 24 V, VIN                |

### Interface

|      |                           |
|------|---------------------------|
| Type | EtherNet TCP/IP, PROFINET |
|------|---------------------------|

### Ethernet

|          |                              |
|----------|------------------------------|
| Function | Configuration / process data |
|----------|------------------------------|

### PROFINET

|          |                              |
|----------|------------------------------|
| Function | Configuration / process data |
|----------|------------------------------|

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 8 Piece(s) |
|-----------------------|------------|

### Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Earthing       |
| Type of connection | Earthing strap |
| Material           | Metal          |

### Connection 2

|                    |                   |
|--------------------|-------------------|
| Function           | Voltage supply    |
| Type of connection | Harting connector |
| Material           | Metal             |

### Connection 3

|                    |                                          |
|--------------------|------------------------------------------|
| Function           | Width measuring light curtain connection |
| Type of connection | Connector                                |
| Thread size        | M12                                      |
| Type               | Male                                     |
| Material           | Metal                                    |
| No. of pins        | 8 -pin                                   |
| Encoding           | A-coded                                  |

### Connection 4

|                    |                                           |
|--------------------|-------------------------------------------|
| Function           | Height measuring light curtain connection |
| Type of connection | Connector                                 |
| Thread size        | M12                                       |
| Type               | Male                                      |
| Material           | Metal                                     |
| No. of pins        | 8 -pin                                    |
| Encoding           | A-coded                                   |

### Connection 5

|                    |                                                                                    |
|--------------------|------------------------------------------------------------------------------------|
| Function           | Rotary encoder connection (not in combination with length measuring light curtain) |
| Type of connection | Connector                                                                          |
| Thread size        | M12                                                                                |
| Type               | Male                                                                               |
| Material           | Metal                                                                              |
| No. of pins        | 8 -pin                                                                             |
| Encoding           | A-coded                                                                            |

### Connection 6

|                    |                                     |
|--------------------|-------------------------------------|
| Function           | External Ethernet TCP/IP connection |
| Type of connection | Connector                           |
| Thread size        | M12                                 |
| Type               | Male                                |
| Material           | Metal                               |
| No. of pins        | 4 -pin                              |
| Encoding           | A-coded                             |

### Connection 7

|                    |                                   |
|--------------------|-----------------------------------|
| Function           | PROFINET IN connection (optional) |
| Type of connection | Connector                         |
| Thread size        | M12                               |
| Type               | Male                              |
| Material           | Metal                             |
| No. of pins        | 4 -pin                            |
| Encoding           | A-coded                           |

### Connection 8

|                    |                                    |
|--------------------|------------------------------------|
| Function           | PROFINET OUT connection (optional) |
| Type of connection | Connector                          |
| Thread size        | M12                                |
| Type               | Male                               |
| Material           | Metal                              |
| No. of pins        | 4 -pin                             |
| Encoding           | A-coded                            |

## Technical data

### Mechanical data

|                     |                                                              |
|---------------------|--------------------------------------------------------------|
| Design              | Cubic                                                        |
| Housing material    | Metal                                                        |
| Metal housing       | Aluminum                                                     |
| Lens cover material | Plastic                                                      |
| Net weight          | 12,750 g                                                     |
| Housing color       | Gray                                                         |
|                     | Red                                                          |
| Note                | Dimensions of individual set items, see dimensioned drawings |

### Operation and display

|                       |                         |
|-----------------------|-------------------------|
| Type of display       | LED                     |
| Number of LEDs        | 3 Piece(s)              |
| Type of configuration | performed via webConfig |
| Operational controls  | Rotary switch           |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | 0 ... 45 °C   |
| Ambient temperature, storage   | -20 ... 70 °C |


### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 90314990 |
| ECLASS 5.1.4          | 27270910 |
| ECLASS 8.0            | 27270910 |
| ECLASS 9.0            | 27270910 |
| ECLASS 10.0           | 27270910 |
| ECLASS 11.0           | 27270910 |
| ECLASS 12.0           | 27270910 |
| ECLASS 13.0           | 27270910 |
| ECLASS 14.0           | 27270910 |
| ECLASS 15.0           | 27270910 |
| ECLASS 16.0           | 27270910 |
| ETIM 5.0              | EC002549 |
| ETIM 6.0              | EC002549 |
| ETIM 7.0              | EC002549 |
| ETIM 8.0              | EC002549 |
| ETIM 9.0              | EC002549 |
| ETIM 10.0             | EC002549 |




## Dimensioned drawings

### Switch cabinet




## Dimensioned drawings

### Rotary encoders



Dimensioned drawings

Mounting bracket



Electrical connection

Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Earthing       |
| Type of connection | Earthing strap |
| Material           | Metal          |

Connection 2

XS1000

|                    |                   |
|--------------------|-------------------|
| Function           | Voltage supply    |
| Type of connection | Harting connector |
| Material           | Metal             |

Connection 3


XS1301

|                    |                                          |
|--------------------|------------------------------------------|
| Function           | Width measuring light curtain connection |
| Type of connection | Connector                                |
| Thread size        | M12                                      |
| Type               | Male                                     |
| Material           | Metal                                    |
| No. of pins        | 8 -pin                                   |
| Encoding           | A-coded                                  |




## Electrical connection

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | IO1            |
| 3   | GND            |
| 4   | IO-Link        |
| 5   | IO2            |
| 6   | IO3            |
| 7   | IO4            |
| 8   | GND            |




| Connection 4       | XS1302                                    |
|--------------------|-------------------------------------------|
| Function           | Height measuring light curtain connection |
| Type of connection | Connector                                 |
| Thread size        | M12                                       |
| Type               | Male                                      |
| Material           | Metal                                     |
| No. of pins        | 8 -pin                                    |
| Encoding           | A-coded                                   |

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | IO1            |
| 3   | GND            |
| 4   | IO-Link        |
| 5   | IO2            |
| 6   | IO3            |
| 7   | IO4            |
| 8   | GND            |



| Connection 5       | XS1400                                                                             |
|--------------------|------------------------------------------------------------------------------------|
| Function           | Rotary encoder connection (not in combination with length measuring light curtain) |
| Type of connection | Connector                                                                          |
| Thread size        | M12                                                                                |
| Type               | Male                                                                               |
| Material           | Metal                                                                              |
| No. of pins        | 8 -pin                                                                             |
| Encoding           | A-coded                                                                            |

| Pin | Pin assignment |
|-----|----------------|
| 1   | U-             |
| 2   | U+             |
| 3   | A              |
| 4   | B              |
| 5   | N              |
| 6   | A inv.         |
| 7   | B inv.         |
| 8   | N inv.         |
| 9   | Shield         |



## Electrical connection


### Connection 6

### XETH1

|                    |                                     |
|--------------------|-------------------------------------|
| Function           | External Ethernet TCP/IP connection |
| Type of connection | Connector                           |
| Thread size        | M12                                 |
| Type               | Male                                |
| Material           | Metal                               |
| No. of pins        | 4 -pin                              |
| Encoding           | A-coded                             |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |




### Connection 7

### XS1100

|                    |                                   |
|--------------------|-----------------------------------|
| Function           | PROFINET IN connection (optional) |
| Type of connection | Connector                         |
| Thread size        | M12                               |
| Type               | Male                              |
| Material           | Metal                             |
| No. of pins        | 4 -pin                            |
| Encoding           | A-coded                           |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |




### Connection 8

### XS1101


|                    |                                    |
|--------------------|------------------------------------|
| Function           | PROFINET OUT connection (optional) |
| Type of connection | Connector                          |
| Thread size        | M12                                |
| Type               | Male                               |
| Material           | Metal                              |
| No. of pins        | 4 -pin                             |
| Encoding           | A-coded                            |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |



Diagrams



x Total measuring length from width and height measuring light curtain [mm]  
y Max. conveyor speed [m/s]

Notes

Observe intended use!


- This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

Accessories

Connection technology - Interconnection cables

|  | Part no. | Designation                 | Article               | Description                                                                                                                                                                                                                             |
|--|----------|-----------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50135082 | KSS ET-M12-4A-RJ45-A-P7-100 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 10,000 mm<br>Sheathing material: PUR |

## Accessories

|                                                                                  | Part no. | Designation                 | Article               | Description                                                                                                                                                                                                                             |
|----------------------------------------------------------------------------------|----------|-----------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50135083 | KSS ET-M12-4A-RJ45-A-P7-150 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 15,000 mm<br>Sheathing material: PUR |
|                                                                                  | 50135084 | KSS ET-M12-4A-RJ45-A-P7-300 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 30,000 mm<br>Sheathing material: PUR |

## Mounting technology - Other

|                                                                                    | Part no. | Designation   | Article             | Description                                                                                                                                                                                                                                                           |
|------------------------------------------------------------------------------------|----------|---------------|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|   | 50143670 | BT 708M-MRSET | Mounting device set | Contains: Mounting material, Mounting profiles<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|                                                                                    | 50143671 | BT 70EM-MRSET | Mounting device set | Contains: Mounting material, Mounting profiles<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|  | 50143669 | BT 710M-MRSET | Mounting device set | Contains: Mounting profiles, Mounting material<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|                                                                                    | 50142039 | BT 712M-MRSET | Mounting device set | Contains: Mounting profiles, Mounting material<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |

### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.