


## Technical data sheet Interconnection cable

Part no.: 50136760

KDS U-M12-5A-M12-5A-V1-150

### Contents

- Technical data
- Electrical connection
- Circuit diagrams
- Accessories



For illustration purposes only



## Technical data

### Basic data

|             |                    |
|-------------|--------------------|
| Application | Chemical resistant |
|-------------|--------------------|

### Connection

#### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Female    |
| No. of pins        | 5 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |
| Connector, LED     | No        |

#### Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Male      |
| No. of pins        | 5 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |

#### Cable properties

|                                   |                                                                                                      |
|-----------------------------------|------------------------------------------------------------------------------------------------------|
| Number of conductors              | 5 Piece(s)                                                                                           |
| Wire cross section                | 0.34 mm <sup>2</sup>                                                                                 |
| Sheathing color                   | Black                                                                                                |
| Shielded                          | No                                                                                                   |
| Silicone-free                     | Yes                                                                                                  |
| Cable design                      | Interconnection cable                                                                                |
| Cable diameter (external)         | 5 mm                                                                                                 |
| Cable length                      | 15,000 mm                                                                                            |
| Sheathing material                | PVC                                                                                                  |
| Suitability for drag chains       | No                                                                                                   |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone and lead, easily machine-processable                                  |
| Resistance of the outer sheathing | Good oil, gasoline and chemical resistance, flame retardant in accordance with UL 1581 VW1 / CSA FT1 |

### Mechanical data

|                    |       |
|--------------------|-------|
| Width across flats | 13 mm |
| Net weight         | 560 g |

### Operation and display

### Certifications

|                      |         |
|----------------------|---------|
| Degree of protection | IP 65   |
|                      | IP 67   |
| Approvals            | c UL US |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |

## Electrical connection


### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Female    |
| No. of pins        | 5 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |
| Connector, LED     | No        |

### Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Male      |
| No. of pins        | 5 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |

Circuit diagrams



Accessories

General

|                                                                                    | Part no. | Designation   | Article | Description                                                                                                                                   |
|------------------------------------------------------------------------------------|----------|---------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50132266 | TT-Set 0,6-13 | Tool    | Type: Torque key<br>Width across flats: 13 mm<br>Torque: 0.6 N·m<br>Material: Plastic, Stainless steel<br>Ambient temperature: -40 ... 120 °C |

Note

|                                                                                    |                                                                                                                           |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
|  | A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page. |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|