

Technical data sheet Reflector

Part no.: 50113421

TKS 50x50.UV.HT

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Special version

Special version	Heat resistant
-----------------	----------------

Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	51.5 mm
Mounting dimension, height	72 mm
Mounting dimension, thickness	8.7 mm
Reflective surface, height	48 mm
Reflective surface, width	47.25 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Coating	UV-protection
Net weight	25 g
Type of fastening	Adhesive Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 120 °C
--------------------------------	----------------

Certifications

Degree of protection	IP 40
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467

Dimensioned drawings

All dimensions in millimeters

