

## Technical data sheet

### Tower light

Part no.: 50138251

A7-V1-MP1-BZ2-S-DS-ROG-T-100

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Notes
- Accessories



For illustration purposes only



## Technical data

### Basic data

Series	A7
Type of signaling	Optical and acoustic

### Electrical data

Life expectancy	> 100,000 h
-----------------	-------------

#### Performance data

Supply voltage $U_B$	24 V, DC, 10 %
Current consumption, max.	160 mA

### Connection

Number of connections	2 Piece(s)
-----------------------	------------

Notes	Protected against accidental interchanges: Actuation of the colors is performed via PINs, thus, the calotte position can be freely selected (see operating instructions). The individual colors are actuated via VCC (PNP)
-------	---

#### Connection 1

Function	Voltage supply
Type of connection	Cable
Cable length	1,500 mm
Number of conductors	6 -wire

#### Connection 2

Type of connection	Open end
--------------------	----------

### Mechanical data

Design	Cylindrical
Dimension ( $\varnothing$ x L)	70 mm x 347 mm
Housing material	Metal Plastic
Plastic housing	PC-ABS
Metal housing	Aluminum
Net weight	611 g
Housing color	Black Gray
Type of fastening, at system	Screw type / horizontal
Type of illuminant	LED/24V
Lens modules	4 pieces, ready-made
Signal image	Continuous light
Angle of radiation	360°
Sequence of the modules (ascending)	Green, orange, red, single sound buzzer

### Environmental data

Ambient temperature, operation	-10 ... 60 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 66
Approvals	CE CSA

### Acoustic data


Tone type	Continuous tone
Sound pressure	105 dB
Number of tones	1 Piece(s)

### Classification

Customs tariff number	85318070
ECLASS 5.1.4	27371230
ECLASS 8.0	27371230
ECLASS 9.0	27371220
ECLASS 10.0	27371230
ECLASS 11.0	27371230
ECLASS 12.0	27371230
ECLASS 13.0	27371230
ECLASS 14.0	27371230
ECLASS 15.0	27371230
ECLASS 16.0	27371230
ETIM 5.0	EC001042
ETIM 6.0	EC001042
ETIM 7.0	EC001042
ETIM 8.0	EC001042
ETIM 9.0	EC001042
ETIM 10.0	EC001042
UNSPSC 26.08	39111714

# Dimensioned drawings

All dimensions in millimeters



## Electrical connection

### Connection 1

Function	Voltage supply
Type of connection	Cable
Cable length	1,500 mm
Sheathing material	PVC
Cable color	Gray
Number of conductors	6 -wire
Wire cross section	0.34 mm <sup>2</sup>

## Electrical connection

Conductor color	Conductor assignment
Black	GND
Red	VCC / Light color: red
Green	VCC / Light color: green
Orange	VCC / Light color: yellow/orange
White	VCC / Light color: white / buzzer
Blue	VCC / Light color: blue

### Connection 2

Type of connection	Open end
--------------------	----------

### Connection 3

Function	Connection to device
Type of connection	Terminal
Type of terminal	Tension spring technology
No. of pins	6 -pin

Terminal	Assignment
B	Blue
G	Green
A	orange/yellow
R	Red
0 V	GND
W	white/buzzer

## Notes




**Observe intended use!**



- ⚠ This product is not a safety sensor and is not intended as personnel protection.
- ⚠ The product may only be put into operation by competent persons.
- ⚠ Only use the product in accordance with its intended use.

## Accessories

### Muting - Mounting systems

	Part no.	Designation	Article	Description
	50142896	A7-MW2	Tower light element	Design: L shape Version: Angle, L-shape Fastening, at system: Through-hole mounting

## Accessories

### Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.