


## Technical data sheet Interconnection cable

Part no.: 50155263

KDS 05 U-M8-4A-M8-4A-P1-020

### Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



## Technical data

### Basic data

|             |                             |
|-------------|-----------------------------|
| Application | Oil and lubricant resistant |
|-------------|-----------------------------|

### Electrical data

|                   |            |
|-------------------|------------|
| Performance data  |            |
| Operating voltage | 30 V AC/DC |

### Connection

#### Connection 1

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| Type of connection   | Connector                                                                   |
| Thread size          | M8                                                                          |
| Type                 | Female                                                                      |
| Handle body material | PUR                                                                         |
| No. of pins          | 4 -pin                                                                      |
| Encoding             | A-coded                                                                     |
| Version              | Axial                                                                       |
| Connector, LED       | No                                                                          |
| Lock                 | Screw fitting, nickel-plated brass, recommended torque 0.4 Nm, self-locking |

#### Connection 2

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| Type of connection   | Connector                                                                   |
| Thread size          | M8                                                                          |
| Type                 | Male                                                                        |
| Handle body material | PUR                                                                         |
| No. of pins          | 4 -pin                                                                      |
| Encoding             | A-coded                                                                     |
| Version              | Axial                                                                       |
| Lock                 | Screw fitting, nickel-plated brass, recommended torque 0.4 Nm, self-locking |

#### Cable properties

|                             |                                                                                             |
|-----------------------------|---------------------------------------------------------------------------------------------|
| Number of conductors        | 4 Piece(s)                                                                                  |
| Wire cross section          | 0.25 mm <sup>2</sup>                                                                        |
| AWG                         | 24                                                                                          |
| Sheathing color             | Black                                                                                       |
| Shielded                    | No                                                                                          |
| Silicone-free               | Yes                                                                                         |
| Cable design                | Interconnection cable                                                                       |
| Cable diameter (external)   | 4.7 mm                                                                                      |
| Cable length                | 2,000 mm                                                                                    |
| Sheathing material          | PUR                                                                                         |
| Wire insulation             | PP                                                                                          |
| Suitability for drag chains | Yes                                                                                         |
| Traverse rate               | Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 5m/s <sup>2</sup> |

|                                   |                                                                                                                      |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------|
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------|

|                                   |                                                                                                                                                                                                                 |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                     |                                                     |
|---------------------|-----------------------------------------------------|
| Torsion suitability | ±180° / m (max. 2 mio. cycles with 35 cycles / min) |
|---------------------|-----------------------------------------------------|

### Mechanical data

|                                         |                          |
|-----------------------------------------|--------------------------|
| Width across flats                      | 9 mm                     |
| Bending cycles                          | 5,000,000 Piece(s)       |
| Bending radius, flexible laying, min.   | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 5 x cable diameter  |

### Operation and display

### Environmental data

|                                                |               |
|------------------------------------------------|---------------|
| Ambient temperature, operation, flexible use   | -25 ... 80 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

### Certifications

|                      |         |
|----------------------|---------|
| Degree of protection | IP 67   |
| Approvals            | CSA     |
|                      | UL      |
| UL file number       | E366145 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |

Electrical connection

Connection 1

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| Type of connection   | Connector                                                                   |
| Thread size          | M8                                                                          |
| Type                 | Female                                                                      |
| Handle body material | PUR                                                                         |
| No. of pins          | 4 -pin                                                                      |
| Encoding             | A-coded                                                                     |
| Version              | Axial                                                                       |
| Connector, LED       | No                                                                          |
| Lock                 | Screw fitting, nickel-plated brass, recommended torque 0.4 Nm, self-locking |

Connection 2

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| Type of connection   | Connector                                                                   |
| Thread size          | M8                                                                          |
| Type                 | Male                                                                        |
| Handle body material | PUR                                                                         |
| No. of pins          | 4 -pin                                                                      |
| Encoding             | A-coded                                                                     |
| Version              | Axial                                                                       |
| Lock                 | Screw fitting, nickel-plated brass, recommended torque 0.4 Nm, self-locking |

Circuit diagrams

Wiring schematic

