

## Technical data sheet

### Clamp

Part no.: 50134200

MC 004K

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Basic data

|                            |                                |
|----------------------------|--------------------------------|
| Suitable for product group | Switching sensors, cylindrical |
| Suitable for               | 204 series sensors             |
|                            | Sensors with M4 design         |

Mechanical data

|                                                |                       |
|------------------------------------------------|-----------------------|
| Inner diameter                                 | 4 mm                  |
| Chemical designation, plastic mounting devices | Polyamide (PA 66)     |
| Design of mounting device                      | Mounting clamp        |
| Type of fastening, at system                   | Through-hole mounting |
| Type of fastening, at device                   | Clampable             |
| Type of mounting device                        | Rigid                 |
| Mounting device material                       | Plastic               |

Environmental data

|                                |             |
|--------------------------------|-------------|
| Ambient temperature, operation | 0 ... 80 °C |
|--------------------------------|-------------|

Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 39174000 |
| ECLASS 5.1.4          | 27279202 |
| ECLASS 8.0            | 27279202 |
| ECLASS 9.0            | 27273701 |
| ECLASS 10.0           | 27273701 |
| ECLASS 11.0           | 27273701 |
| ECLASS 12.0           | 27273701 |
| ECLASS 13.0           | 27273701 |
| ECLASS 14.0           | 27273701 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |

Dimensioned drawings

All dimensions in millimeters

