

Technical data sheet

Reflector

Part no.: 50110569

TKS 20x75

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

Technical data

Mechanical data

Design	Rectangular
Triple reflector size	2.6 mm
Mounting dimension, width	20 mm
Mounting dimension, height	76 mm
Mounting dimension, thickness	11 mm
Reflective surface, height	70 mm
Reflective surface, width	15 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Type of fastening	M4 x 19 mm threaded pin

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Dimensioned drawings

All dimensions in millimeters

