

## Technical data sheet

### Transponder

Part no.: 50102916

TFM 05 1110.210

#### Contents

- Technical data
- Dimensioned drawings
- Notes
- Further information
- Accessories



Figure can vary



# Technical data

## Basic data

Series	TFM
Suitable for	RFM
Chip	I-CodeSLI
Working frequency	13.56 MHz

## Electrical data

### Performance data

Memory access	Read/Write
Memory size	112 B
Memory block	28 Piece(s)
Memory block size	4 B
Storage time	50 ms

## Certifications

Standards applied	ISO 15693
-------------------	-----------

## Mechanical data

Design	Disc
Thickness	2.5 mm
Outer diameter	50 mm
Inner diameter	4.2 mm
Housing material	Plastic
Plastic housing	PC
Net weight	10 g

## Environmental data

Ambient temperature, operation	-20 ... 75 °C
Ambient temperature, storage	-30 ... 120 °C

## Certifications


Degree of protection	IP 67
----------------------	-------

## Classification

Customs tariff number	85235200
eCl@ss 5.1.4	27289200
eCl@ss 8.0	27289290
eCl@ss 9.0	27280402
eCl@ss 10.0	27280402
eCl@ss 11.0	27280402
ETIM 5.0	EC002498
ETIM 6.0	EC002996
ETIM 7.0	EC002996

# Dimensioned drawings

All dimensions in millimeters



# Notes


<b>Observe intended use!</b>	
	<ul style="list-style-type: none"> <li>⌘ This product is not a safety sensor and is not intended as personnel protection.</li> <li>⌘ The product may only be put into operation by competent persons.</li> <li>⌘ Only use the product in accordance with its intended use.</li> </ul>

## Further information

- Under certain circumstances, metal in the reading field reduces the operating range considerably.

## Accessories

### Mounting technology - Other

	Part no.	Designation	Article	Description
	50107103	Spacer 50 HT	Spacer	Design, housing: Hollow cylinder Outer diameter: 50 mm Inner diameter: 5 mm Housing material: Plastic, PA 66

#### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.