

Technical data sheet Stationary bar code reader

Part no.: 50147478

BCL 658i SF 102



Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Part number code
- Notes
- Accessories













Technical data



Series	BCL 600i
Functions	
unctions	Alignment mode
	AutoConfig
	AutoControl
	AutoReflAct
	Code fragment technology
	LED indicator
	Reference code comparison
haraatariatia naramatara	, , , , , , , , , , , , , , , , , , , ,
haracteristic parameters	42.4 years
•••	42.4 yours
ead data	
ode types, readable	2/5 Interleaved
	Codabar
	Code 128
	Code 39
	Code 93
	EAN 128
	EAN 8/13
	EAN Addendum
	GS1 Databar Expanded
	GS1 Databar Limited
	GS1 Databar Omnidirectiona
	UPC
canning rate, typical	800 scans/s
ar codes per reading gate, max. umber	64 Piece(s)
Optical data	
eading distance	450 1,450 mm
_	Laser, Blue
ight source	Laser, Blue 405 nm
ight source /avelength	405 nm 2, IEC/EN 60825-1:2014
ght source avelength aser class ansmitted-signal shape	405 nm
ight source Vavelength .aser class ransmitted-signal shape Isable opening angle (reading field	405 nm 2, IEC/EN 60825-1:2014
ight source /avelength aser class ransmitted-signal shape sable opening angle (reading field pening)	405 nm 2, IEC/EN 60825-1:2014 Continuous
ight source /avelength aser class ransmitted-signal shape sable opening angle (reading field pening) ar code contrast (PCS)	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 °
ight source //avelength aser class ransmitted-signal shape sable opening angle (reading field pening) ar code contrast (PCS)	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 °
ight source /avelength aser class ransmitted-signal shape sable opening angle (reading field pening) ar code contrast (PCS) lodulus size eading method	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm
dight source Vavelength aser class Transmitted-signal shape Jable opening angle (reading field opening) Bar code contrast (PCS) Modulus size Reading method Beam deflection	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm Line scanner
Light source Vavelength Laser class Fransmitted-signal shape Jable opening angle (reading field opening) Bar code contrast (PCS) Modulus size Reading method Beam deflection Light beam exit	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm Line scanner Via rotating polygon wheel
Light source Wavelength Laser class Transmitted-signal shape Usable opening angle (reading field opening) Bar code contrast (PCS) Wodulus size Reading method Beam deflection Light beam exit	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm Line scanner Via rotating polygon wheel
Light source Wavelength Laser class Fransmitted-signal shape Usable opening angle (reading field opening) Bar code contrast (PCS) Modulus size Reading method Beam deflection Light beam exit	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm Line scanner Via rotating polygon wheel Front
ight source Wavelength asser class ransmitted-signal shape Isable opening angle (reading field pening) Isar code contrast (PCS) Indulus size Iteading method Iteam deflection Ight beam exit Itectrical data	405 nm 2, IEC/EN 60825-1:2014 Continuous 60 ° 60 % 0.3 0.5 mm Line scanner Via rotating polygon wheel Front

0 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	00 1
Output current, max.	60 mA
Number of inputs/outputs selecta	
Voltage type, outputs	DC
Switching voltage, outputs	Typ. U _B / 0 V
Voltage type, inputs	DC
Switching voltage, inputs Input current, max.	Typ. U _B / 0 V 8 mA
input current, max.	OTTA
nterface	
уре	EtherNet IP
EtherNet IP	
Function	Process
Address assignment	DHCP
	Manual address assignment
Switch functionality	Integrated
Transmission speed	10 Mbit/s
	100 Mbit/s
Service interface	
уре	USB
USB	
Function	Configuration via software
	Service
Connection	
lumber of connections	5 Piece(s)
Connection 1	
Function	Service interface
Type of connection	USB
Designation on device	SERVICE
Connector type	USB 2.0 Standard-A
Connection 2	
Connection 2 Function	Signal IN
Function	Signal OUT
Function Type of connection	Signal OUT Connector
Function Type of connection Designation on device	Signal OUT Connector SW IN/OUT
Function Type of connection Designation on device Thread size	Signal OUT Connector SW IN/OUT M12
Function Type of connection Designation on device Thread size Type	Signal OUT Connector SW IN/OUT M12 Female
Function Type of connection Designation on device Thread size Type Material	Signal OUT Connector SW IN/OUT M12 Female Metal
Function Type of connection Designation on device Thread size Type Material No. of pins	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin
Function Type of connection Designation on device Thread size Type Material	Signal OUT Connector SW IN/OUT M12 Female Metal
Function Type of connection Designation on device Thread size Type Material No. of pins	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3 Function	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3 Function Type of connection	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded PWR / SW IN / OUT Connector
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3 Function Type of connection Designation on device	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded PWR / SW IN / OUT Connector PWR
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3 Function Type of connection Designation on device Thread size	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded PWR / SW IN / OUT Connector PWR M12
Function Type of connection Designation on device Thread size Type Material No. of pins Encoding Connection 3 Function Type of connection Designation on device Thread size Type	Signal OUT Connector SW IN/OUT M12 Female Metal 5 -pin A-coded PWR / SW IN / OUT Connector PWR M12 Male

Technical data

Operational controls



Connection 4	DUO IN		
Function	BUS IN		
Type of connection	Connector		
Designation on device	HOST / BUS IN		
Thread size	M12		
Туре	Female		
Material	Metal		
No. of pins	4 -pin		
Encoding	D-coded		
Connection 5			
Function	BUS OUT		
Type of connection	Connector		
Designation on device	BUS OUT		
Thread size	M12		
Туре	Female		
No. of pins	4 -pin		
Machanical data			
Mechanical data	0.11		
Design	Cubic		
Design Dimension (W x H x L)	123.5 mm x 63 mm x 104.2 mm		
Design Dimension (W x H x L) Housing material	123.5 mm x 63 mm x 104.2 mm Metal		
Design Dimension (W x H x L) Housing material Metal housing	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum		
Design Dimension (W x H x L) Housing material	123.5 mm x 63 mm x 104.2 mm Metal		
Design Dimension (W x H x L) Housing material Metal housing	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color Type of fastening	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color Type of fastening Operation and display	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread Via optional mounting device		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color Type of fastening Operation and display	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread Via optional mounting device LED Monochromatic graphical display,		
Design Dimension (W x H x L) Housing material Metal housing Lens cover material Net weight Housing color Type of fastening Operation and display Type of display	123.5 mm x 63 mm x 104.2 mm Metal Diecast aluminum Glass 1,400 g Red Silver Dovetail grooves Mounting thread Via optional mounting device LED Monochromatic graphical display, 128x64 pixel, with background lighting		

Button(s)

Via service interface


Ambient temperature, operation	0 40 °C
Ambient temperature, storage	-20 70 °C
Relative humidity (non-condensing)	90 %
Extraneous light tolerance on the bar code, max.	2,000 lx
Certifications	
Degree of protection	IP 65
Protection class	III
Approvals	c UL US
Test procedure for EMC in accordance	EN 55022
with standard	EN 61000-4-2, -3, -4, -6
	EN 61000-6-2
Test procedure for shock in accordance with standard	IEC 60068-2-27, test Ea
Test procedure for continuous shock in accordance with standard	IEC 60068-2-29, test Eb
Test procedure for vibration in accordance with standard	IEC 60068-2-6, test Fc
Classification	
Customs tariff number	84719000


Classification	
Customs tariff number	84719000
ECLASS 5.1.4	27280102
ECLASS 8.0	27280102
ECLASS 9.0	27280102
ECLASS 10.0	27280102
ECLASS 11.0	27280102
ECLASS 12.0	27280102
ECLASS 13.0	27280102
ECLASS 14.0	27280102
ECLASS 15.0	27280102
ETIM 5.0	EC002550
ETIM 6.0	EC002550
ETIM 7.0	EC002550
ETIM 8.0	EC002550
ETIM 9.0	EC002550
ETIM 10.0	EC002550


Dimensioned drawings


Leuze

All dimensions in millimeters









Electrical connection

Connection 1 SERVICE

Function	Service interface
Type of connection	USB
Connector type	USB 2.0 Standard-A

Pin	Pin assignment
1	+5 V DC
2	DATA-
3	DATA+
4	GND


4/10

Electrical connection



Connection 2	SW IN/OUT
Function	Signal IN
	Signal OUT
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	5 -pin
Encoding	A-coded


Pin	Pin assignment
1	VOUT
2	SWIO 1
3	GND
4	SWIO 2
5	FE



Connection 3	PWF

Function	PWR / SW IN / OUT
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded


Pin	Pin assignment
1	VIN
2	SWIO 3
3	GND
4	SWIO 4
5	FE



Connection 4 HOST / BUS IN

Function	BUS IN
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded

Pin	Pin assignment
1	TD+
2	RD+
3	TD-
4	RD-




Electrical connection




Connection 5	BUS OUT	
Function	BUS OUT	
Type of connection	Connector	
Thread size	M12	
Туре	Female	
Material	Metal	
No. of pins	4 -pin	
Encoding	D-coded	

Pin	Pin assignment
1	TD+
2	RD+
3	TD-
4	RD-



Diagrams

Reading field curve - Low Density



- Reading field width [mm]
- Reading field distance [mm]
- Module = 0.3 mm: 600 mm 1050 mm (450 mm depth of field)
- Module = 0.35 mm: 500 mm 1200 mm (700 mm depth of field)
- Module = 0.5 mm: 450 mm 1450 mm (1000 mm depth of field)

Operation and display



LED	Display	Meaning
1 PWR	Off	No supply voltage
	Green, flashing	Initialization
	Green, continuous light	Device OK
	Orange, flashing	Service operation
	Orange, continuous light	Reset
	Red, flashing	Device OK, warning set
	Red, continuous light	Device error
2 NET	Off	No supply voltage
	Green, flashing	BUS initialization
	Green, continuous light	Bus operation ok
	Orange, flashing	Service mode
	Orange, continuous light	Reset
	Red, flashing	Communication error
	Red, continuous light	Network error

Part number code

Part designation: BCL XXXX YYZ AAA B

BCL	Operating principle BCL: bar code reader
XXXX	Series/interface (integrated fieldbus technology) 600i: RS 232/RS 422/ RS 485 (multiNet master) 601i: RS 485 (multiNet slave) 604i: PROFIBUS DP 608i: Ethernet 648i: PROFINET 658i: EtherNet/IP
YY	Scanning principle S: line scanner (single line) O: oscillating-mirror scanner (oscillating mirror)
Z	Optics N: High Density (close) M: Medium Density (medium distance) F: Low Density (remote) L: Long Range (very large distances)
AAA	Beam exit 100: lateral 102: front
ВВ	Special equipment H: with heating

Note



☼ A list with all available device types can be found on the Leuze website at www.leuze.com.

Notes



Observe intended use!



- 🖔 This product is not a safety sensor and is not intended as personnel protection.
- \$ Only use the product in accordance with its intended use.

Notes





ATTENTION! LASER RADIATION - CLASS 2 LASER PRODUCT



Do not stare into beam!

The device satisfies the requirements of IEC/EN 60825-1:2014 safety regulations for a product of laser class 2 as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 56 from May 08, 2019.

- 🔖 Never look directly into the laser beam or in the direction of reflected laser beams! If you look into the beam path over a longer time period, there is a risk of injury to the retina.
- ♥ Do not point the laser beam of the device at persons!
- 🔖 Interrupt the laser beam using a non-transparent, non-reflective object if the laser beam is accidentally directed towards a person.
- When mounting and aligning the device, avoid reflections of the laser beam off reflective surfaces!
- 🔖 CAUTION! The use of operating and adjusting devices other than those specified here or the carrying out of differing procedures may lead to dangerous exposure to radiation!
- Observe the applicable statutory and local laser protection regulations.
- \$ The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device. Repairs must only be performed by Leuze electronic GmbH + Co. KG.

NOTE



Affix laser information and warning signs!

Laser information and warning signs are affixed to the device. In addition, self-adhesive laser information and warning signs (stick-on labels) are supplied in several languages

- "Affix the laser information sheet to the device in the language appropriate for the place of use. When using the device in the US, use the stick-on label with the "Complies with 21 CFR 1040.10" note.
- 🌣 Affix the laser information and warning signs near the device if no signs are attached to the device (e.g. because the device is too small) or if the attached laser information and warning signs are concealed due to the installation position.
- Affix the laser information and warning signs so that they are legible without exposing the reader to the laser radiation of the device or other optical radiation.

Accessories

Connection technology - Connection cables

Part no.	Designation	Article	Description
50132079	KD U-M12-5A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC

Connection technology - Interconnection cables

		Part no.	Designation	Article	Description
0.0	, , , , , , , , , , , , , , , , , , ,	50107726	KB USB A - USB A	Interconnection cable	Suitable for interface: USB Connection 1: USB Connection 2: USB Shielded: Yes Cable length: 1,800 mm Sheathing material: PVC

The Sensor People In der Braike 1, D-73277 Owen/Germany Phone: +49 7021 573-0 • Fax: +49 7021 573-199 eng • 2025-04-06

Leuze electronic GmbH + Co. KG

info@leuze.com • www.leuze.com

We reserve the right to make technical changes

Accessories



	Part no.	Designation	Article	Description
	50137078	KSS ET-M12-4A- M12-4A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: Connector, M12, Axial, Male, D-coded, 4 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR
	50135081	KSS ET-M12-4A- RJ45-A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: RJ45 Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Mounting technology - Other

Part no.	Designation	Article	Description
50111224	BT 59	Mounting bracket	Fastening, at system: Groove mounting Mounting bracket, at device: Clampable Material: Metal Shock absorber: No

Services

	Part no.	Designation	Article	Description
	S981020	CS30-E-212	Hourly rate	Details: Compilation of the application data, selection and suggestion of suitable sensor system, drawing prepared as assembly sketch. Conditions: Completed questionnaire or project specifications with a description of the application have been provided.
	S981014	CS30-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
	S981019	CS30-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.
 	S981021	CS30-V-212	Hourly rate	Details: REA evaluation with creation of a test report, evaluation of the code quality. Conditions: Original bar codes to be provided by the client.

Accessories



Note



🔖 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.