Technical data sheet Optical distance sensor Part no.: 50137823 ODS9L2.8/L6X-200-M12



The Sensor People In der Braike 1, D-73277 Owen/Germany

Leuze electronic GmbH + Co. KG

info@leuze.com • www.leuze.com changes Phone: +49 7021 573-0 • Fax: +49 7021 573-199 eng • 2025-04-06

We reserve the right to make technical



Technical data

Basic data

Series	9
Application	Fill-level monitoring
	Length measurement in material cutting
	Object measurement
Type of scanning system	Against object

Optical data

Collimated
Laser, Red
650 nm
2, IEC/EN 60825-1:2014
Pulsed
22,000 µs
1 mm [200 mm]
Round

Measurement data

Measurement range	50 200 mm
Resolution	0.01 mm with measurement range of 50 mm 100 mm
	0.1 mm with measurement range of 100 mm 200 mm
Resolution	0.1 mm
Accuracy, short range	0.5 %50 100 mm
Accuracy, distant range	1 %100 200 mm
Reference value, accuracy	Measurement distance
Reproducibility (1 sigma)	0.05 mm
Temperature drift	0.02 %/K
Referencing	No
Optical distance measurement prin- ciple	Triangulation

Electrical data

Protective circuit

Performance data Supply voltage U_B Residual ripple Open-circuit current

18 ... 30 V, DC 0 ... 15 %, From U_B

Polarity reversal protection

Short circuit protected

Transient protection

0 ... 50 mA

Outputs

Number of digital switching outputs 2 Piece(s)

Switching outputs Voltage type Switching voltage

DC high: ≥(U_B -2V) low: ≤ 2 V

Switching output 1 Assignment Switching element Switching principle

Switching output 2 Assignment Switching element Switching principle Connection 1, pin 4 Transistor, Push-pull

IO-Link / light switching (PNP)/dark switching (NPN)

Connection 1, pin 2 Transistor, Push-pull Light switching (PNP)/dark switching (NPN)

Time behavior Response time 1 ms, Under constant ambient conditions, 90% diffuse reflection, standard measure mode 300 ms Readiness delay Interface Туре IO-Link **IO-Link** COM mode COM3 Smart sensor profile Profile COM3 = 0.5 ms Min. cycle time 2.V Frame type Port type А V1.1 Specification SIO-mode support Yes Process data IN 4 byte 8 bit Process data OUT **Dual Channel** Yes Connection Number of connections 1 Piece(s) **Connection 1** Function Signal OUT Voltage supply Type of connection Connector, Turning, 90° Thread size M12 Туре Male Material Plastic No. of pins 5 -pin Encoding A-coded Mechanical data Design Cubic Dimension (W x H x L) 21 mm x 50 mm x 50 mm Housing material Plastic Lens cover material Glass Net weight 50 g Housing color Red Type of fastening Through-hole mounting Via optional mounting device **Operation and display** Type of display LED OLED display Number of LEDs 2 Piece(s) **Operational controls** Control buttons PC software **Environmental data** -20 ... 50 °C Ambient temperature, operation -30 ... 70 °C Ambient temperature, storage 20,000 lx, EN 60947-5-2 Ambient light sensitivity Certifications IP 67 Degree of protection Protection class Ш Approvals UL

Leuze electronic GmbH + Co. KG The Sensor People In der Braike 1, D-73277 Owen/Germany

Leuze


Technical data

Customs tariff number	90318020
ECLASS 5.1.4	27270801
ECLASS 8.0	27270801
ECLASS 9.0	27270801
ECLASS 10.0	27270801
ECLASS 11.0	27270801
ECLASS 12.0	27270916
ECLASS 13.0	27270916
ECLASS 14.0	27270916
ECLASS 15.0	27270916
ETIM 5.0	EC001825
ETIM 6.0	EC001825
ETIM 7.0	EC001825
ETIM 8.0	EC001825
ETIM 9.0	EC001825
ETIM 10.0	EC001825

Leuze

Dimensioned drawings

All dimensions in millimeters



Leuze

Electrical connection

Connection 1


Function	Signal OUT
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Plastic
No. of pins	5 -pin
Encoding	A-coded

Electrical connection

Pin	Pin assignment	
1	18 30 V DC +	
2	OUT 2	
3	GND	
4	IO-Link / OUT 1	
5	n.c.	

Diagrams

Accuracy of measurement



Operation and display


LED	Display	Meaning
1	Green, continuous light	Ready
2	Yellow, continuous light	Object in the measurement range

Part number code

Part designation: ODS9XX.Y/ZAB-CCC-DDD

ODS9	Operating principle Optical distance sensor of the 9 series
ХХ	Light source L2: laser class 2 L1: laser class 1
Y	Equipment 8: OLED display and membrane keyboard for configuration
z	Switching output/function OUT 1/IN: Pin 4 or black conductor L: IO-Link
A	Switching output / function OUT 2/IN: pin 2 or white conductor A: Analog output 6: push-pull switching output, PNP light switching, NPN dark switching
В	Switching output / function OUT 3/IN: Pin 5 X: pin not used 6: push-pull switching output, PNP light switching, NPN dark switching K: Multifunction input (factory setting: deactivation input)





Part number code



CCC	Operating range 100: operating range 50 100 mm 200: operating range 50 200 mm 450: operating range 50 450 mm 650: operating range 50 650 mm 1050: operating range 50 1050 mm
DDD	Electrical connection M12: M12 connector
	Note
0	∜ A list with all available device types can be found on the Leuze website at www.leuze.com.

Notes

		Observe intended use!
	~	✤ This product is not a safety sense
	rightarrow The product may only be put int	
	♦ Only use the product in accorda	

This product is not a safety	sensor and is not intended a	s personnel protection.

- only be put into operation by competent persons.
- duct in accordance with its intended use.

ATTENTION! LASER RADIATION - CLASS 2 LASER PRODUCT
Do not stare into beam! The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 2 as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.
Never look directly into the laser beam or in the direction of reflected laser beams! If you look into the beam path over a longer time period, there is a risk of injury to the retina.
t bo not point the laser beam of the device at persons!
the laser beam using a non-transparent, non-reflective object if the laser beam is accidentally directed towards a person.
∜ When mounting and aligning the device, avoid reflections of the laser beam off reflective surfaces!
S CAUTION! The use of operating and adjusting devices other than those specified here or the carrying out of differing procedures may lead to dangerous exposure to radiation!
∜ Observe the applicable statutory and local laser protection regulations.
 The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device. Repairs must only be performed by Leuze electronic GmbH + Co. KG.

NOTE

Affix laser information and warning signs!

- Laser information and warning signs are affixed to the device. In addition, self-adhesive laser information and warning signs (stick-on labels) are supplied in several languages.
- 🗞 "Affix the laser information sheet to the device in the language appropriate for the place of use. When using the device in the US, use the stick-on label with the "Complies with 21 CFR 1040.10" note.
- Affix the laser information and warning signs near the device if no signs are attached to the device (e.g. because the device is too small) or if the attached laser information and warning signs are concealed due to the installation position.
- 🗞 Affix the laser information and warning signs so that they are legible without exposing the reader to the laser radiation of the device or other optical radiation.

Accessories



Connection technology - Connection unit

	Part no.	Designation	Article	Description
Constantial State	50144900	MD 798i-11-82/L5- 2222	IO-Link master	Type: IO-Link master Current consumption, max.: 11,000 mA Switching outputs for each sensor connection: 1 Piece(s) Switching output: Transistor, PNP Interface: IO-Link, Automatic protocol detection, EtherNet IP, Modbus TCP, PROFINET Connections: 12 Piece(s) Sensor connections: 8 Piece(s) Connections for voltage supply: 2 Piece(s) Interface connections: 2 Piece(s) Degree of protection: IP 67, IP 65, IP 69K

Connection technology - Connection cables

	Part no.	Designation	Article	Description
W D	50132077	KD U-M12-5A-V1- 020	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 2.000 mm Sheathing material: PVC
Ŵ	50132079	KD U-M12-5A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC

Mounting technology - Mounting brackets

 Part no.	Designation	Article	Description
50118543	BT 300M.5	Mounting bracket	Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type, Suited for M4 screws Type of mounting device: Adjustable Material: Stainless steel

Mounting technology - Rod mounts

 Part no.	Designation	Article	Description
50117252	BTU 300M-D12	Mounting system	Design of mounting device: Mounting system Fastening, at system: For 12 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type, Suited for M4 screws Type of mounting device: Clampable, Adjustable, Turning, 360° Material: Metal

Accessories

Leuze

	Part no.	Designation	Article	Description
0	50128380	BTU 460M-D12	Mounting system	Design of mounting device: Mounting system Fastening, at system: For 12 mm rod Mounting bracket, at device: Screw type Type of mounting device: Adjustable, Turning, 360° Material: Metal

	Note
6	☆ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.