

Technical data sheet Reflector

Part no.: 50022814

TKS 50X50

Contents

- Technical data



For illustration purposes only

Technical data

Mechanical data

Design	Rectangular
Triple reflector size	4 mm
Mounting dimension, width	51.5 mm
Mounting dimension, height	72 mm
Mounting dimension, thickness	8.7 mm
Reflective surface, height	48 mm
Reflective surface, width	47 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	20 g
Type of fastening	Adhesive
	Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467