

## Technical data sheet

### Mounting bracket

Part no.: 50113549

BT D12M.5

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Basic data

|                            |                                |
|----------------------------|--------------------------------|
| Suitable for product group | Switching sensors, cylindrical |
| Suitable for               | Sensors with M12 design        |

### Mechanical data

|                                                       |                       |
|-------------------------------------------------------|-----------------------|
| Dimension (W x H x L)                                 | 25 mm x 24 mm x 16 mm |
| Inner diameter                                        | 12 mm                 |
| Standard designation, stainless steel mounting device | V2A                   |
| Net weight                                            | 14 g                  |
| Design of mounting device                             | Angle, L-shape        |
| Type of fastening, at system                          | Through-hole mounting |
| Type of fastening, at device                          | Screw type            |
| Type of mounting device                               | Rigid                 |
| Mounting device material                              | Stainless steel       |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 73182900 |
| ECLASS 5.1.4          | 27279202 |
| ECLASS 8.0            | 27279202 |
| ECLASS 9.0            | 27273701 |
| ECLASS 10.0           | 27273701 |
| ECLASS 11.0           | 27273701 |
| ECLASS 12.0           | 27273701 |
| ECLASS 13.0           | 27273701 |
| ECLASS 14.0           | 27273701 |
| ECLASS 15.0           | 27273701 |
| ECLASS 16.0           | 27273701 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |
| ETIM 10.0             | EC003015 |

## Dimensioned drawings

All dimensions in millimeters

