

## Technical data sheet

### Transponder

Part no.: 50127101

TFM 06 1110.210

#### Contents

- Technical data
- Dimensioned drawings
- Notes
- Further information



For illustration purposes only



## Technical data

### Basic data

Series	TFM
Suitable for	RFM
Chip	I-CodeSLI

### Electrical data

#### Performance data

Memory size	112 B
Memory block	112 Piece(s)

### Certifications

Standards applied	ISO 15693
-------------------	-----------

### Mechanical data

Design	Disc
Thickness	10 mm
Outer diameter	56 mm
Inner diameter	4.3 ... 4.9 mm
Housing material	Plastic
Plastic housing	PC
Net weight	20 g
Mounting	On metal

### Environmental data

Ambient temperature, operation	-30 ... 60 °C
Ambient temperature, storage	-30 ... 85 °C

### Certifications


Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	85235200
ECLASS 5.1.4	27289200
ECLASS 8.0	27289290
ECLASS 9.0	27280402
ECLASS 10.0	27280402
ECLASS 11.0	27280402
ECLASS 12.0	27280402
ECLASS 13.0	27280402
ECLASS 14.0	27280402
ECLASS 15.0	27280402
ECLASS 16.0	27280402
ETIM 5.0	EC002498
ETIM 6.0	EC002996
ETIM 7.0	EC002996
ETIM 8.0	EC002996
ETIM 9.0	EC002996
ETIM 10.0	EC002996
UNSPSC 26.08	43211710

## Dimensioned drawings

All dimensions in millimeters



## Notes



**Observe intended use!**



- ⌘ This product is not a safety sensor and is not intended as personnel protection.
- ⌘ The product may only be put into operation by competent persons.
- ⌘ Only use the product in accordance with its intended use.

## Further information

- Under certain circumstances, metal in the reading field reduces the operating range considerably.