

Technical data sheet

Connection cable

Part no.: 50135244

KD PB-M12-4A-P3-100

Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



Technical data

Basic data

| | |
|------------------------|-----------------------------|
| Application | Oil and lubricant resistant |
| Suitable for interface | PROFIBUS DP |

Electrical data

| | |
|-------------------|---------|
| Performance data | |
| Operating voltage | 60 V DC |

Connection

| | |
|-----------------------------------|---|
| Connection 1 | |
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| Handle body material | PUR |
| No. of pins | 5 -pin |
| Encoding | B-coded |
| Version | Axial |
| Connector, LED | No |
| Lock | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |
| Connection 2 | |
| Type of connection | Open end |
| Cable properties | |
| Number of conductors | 2 Piece(s) |
| Wire cross section | 0.64 mm ² |
| AWG | 19 |
| Sheathing color | Violet |
| Shielded | Yes |
| Silicone-free | Yes |
| Cable design | Connection cable (open on one end) |
| Cable diameter (external) | 7.7 mm |
| Cable length | 10,000 mm |
| Sheathing material | PUR |
| Wire insulation | PE |
| Suitability for drag chains | Yes |
| Traverse rate | Max. 3.3 m/s with horiz. traverse path of 5m and max. acceleration of 5m/s ² |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |

Mechanical data

| | |
|---|---------------------------|
| Width across flats | 13 mm |
| Bending cycles | 5,000,000 Piece(s) |
| Bending radius, flexible laying, min. | Min. 12 x cable diameter |
| Bending radius, stationary laying, min. | Min. 7.5 x cable diameter |

Operation and display

Environmental data

| | |
|--|---------------|
| Ambient temperature, operation, flexible use | -20 ... 70 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

Certifications

| | |
|----------------------|-------|
| Degree of protection | IP 65 |
| | IP 67 |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4 | 27279201 |
| ECLASS 8.0 | 27279218 |
| ECLASS 9.0 | 27060311 |
| ECLASS 10.0 | 27060311 |
| ECLASS 11.0 | 27060311 |
| ECLASS 12.0 | 27060311 |
| ECLASS 13.0 | 27060311 |
| ECLASS 14.0 | 27060311 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 |
| ETIM 9.0 | EC001855 |

Electrical connection

Connection 1

| | |
|----------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| Handle body material | PUR |

Electrical connection

Connection 1

| | |
|----------------|--|
| No. of pins | 5 -pin |
| Encoding | B-coded |
| Version | Axial |
| Connector, LED | No |
| Lock | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

| Pin | Conductor color |
|-----|-----------------|
| 1 | n.c. |
| 2 | Green |
| 3 | n.c. |
| 4 | Red |
| 5 | n.c. |



Connection 2

| | |
|--------------------|----------|
| Type of connection | Open end |
|--------------------|----------|

Circuit diagrams

Wiring schematic

