

Technical data sheet

Reflector set

Part no.: 50125455

TKS 40x60.A

Contents

- Technical data



For illustration purposes only

Technical data

Basic data

Contains	10x
----------	-----

Mechanical data

Design	Rectangular
Direction-dependent	No
Triple reflector size	2.3 mm
Mounting dimension, width	40.4 mm
Mounting dimension, height	60 mm
Mounting dimension, thickness	7.2 mm
Reflective surface, height	55.8 mm
Reflective surface, width	36.8 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	36 g
Type of fastening	Adhesive Screw type

Environmental data

Ambient temperature, operation	-20 ... 65 °C
--------------------------------	---------------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ECLASS 16.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467
UNSPSC 26.08	39121551