

Technical data sheet Light curtain receiver Part no.: 50131763 CML730i-R10-1760.R/PN-M12



 Leuze electronic GmbH + Co. KG
 info@leuze.com • www.leuze.com
 changes

 The Sensor People
 In der Braike 1, D-73277 Owen/Germany
 Phone: +49 7021 573-0 • Fax: +49 7021 573-199
 eng • 2025-04-05

1/9

Technical data

Leuze

Series	730
Operating principle	Throughbeam principle
Device type	Receiver
Contains	Accessories for the use of the BT-2R1
Application	Detection of transparent objects
	Object measurement
Special version	
Special version	Crossed-beam scanning
opecial version	Diagonal-beam scanning
	Parallel-beam scanning
	r aranei-beam scanning
Optical data	
Operating range	0.3 9.5 m
Operating range	Guaranteed operating range
Operating range, transparent media	0.3 3.5 m
Operating range limit	0.2 12 m
Operating range limit	Typical operating range
Measurement field length	1,760 mm
Number of beams	176 Piece(s)
Beam spacing	10 mm
Doan opaonig	
Measurement data	
Minimum object diameter	20 mm
Electrical data	
Protective circuit	Polarity reversal protection
	Short circuit protected
	Transient protection
Performance data	
Supply voltage U _B	18 30 V, DC
Residual ripple	0 15 %, From U _B
Open-circuit current	0 350 mA, The specified values refer to the entire package consisting of trans mitter and receiver.
Inputs/outputs selectable	
Output current, max.	100 mA
-	
Input resistance	6,000 Ω
Input resistance Number of inputs/outputs selectable	2 Piece(s)
Input resistance Number of inputs/outputs selectable Type	2 Piece(s) Inputs/outputs selectable
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs	2 Piece(s) Inputs/outputs selectable DC
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs	2 Piece(s) Inputs/outputs selectable DC
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V DC
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V DC high: ≥6V
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs Switching voltage, inputs	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V DC high: ≥6V
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs Switching voltage, inputs Input/output 1	2 Piece(s) Inputs/outputs selectable DC Typ. $U_B / 0 V$ DC high: $\geq 6V$ Iow: $\leq 4 V$
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs Switching voltage, inputs Input/output 1 Activation/disable delay Time behavior	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V DC high: ≥6V Iow: ≤ 4 V 1 ms
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs Switching voltage, inputs Input/output 1 Activation/disable delay Time behavior Readiness delay	2 Piece(s) Inputs/outputs selectable DC Typ. $U_B / 0 V$ DC high: $\geq 6V$ Iow: $\leq 4 V$
Input resistance Number of inputs/outputs selectable Type Voltage type, outputs Switching voltage, outputs Voltage type, inputs Switching voltage, inputs Input/output 1 Activation/disable delay Time behavior	2 Piece(s) Inputs/outputs selectable DC Typ. U _B / 0 V DC high: ≥6V Iow: ≤ 4 V 1 ms 1,500 ms

Туре

PROFINET

PROFINET	
Function	Process
Conformance class	B
Protocol	PROFINET RT
Switch functionality	Integrated
Transmission speed	10 Mbit/s
	100 Mbit/s
Service interface	
Туре	IO-Link
IO-Link	
Function	Configuration via software
	Service
Connection	
Number of connections	3 Piece(s)
Plug outlet	Rear side
6 <i>i i i</i>	
Connection 1 Function	Configuration interface
i uncuon	Configuration interface Connection to transmitter
	Signal IN
	Signal OUT
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	8 -pin
Encoding	A-coded
Composition 0	
Connection 2 Function	BUS IN
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins Encoding	4 -pin D-coded
Encouning	D-coded
Connection 3	
Function	BUS OUT
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded
Mechanical data	
Design	Cubic
Dimension (W x H x L)	29 mm x 35.4 mm x 1,783 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic
Net weight	1,950 g
Housing color	Silver
-	
Type of fastening	Groove mounting
	Via optional mounting device

Technical data

Leuze


Operation and display

Type of display	LED	
	OLED display	
Number of LEDs	4 Piece(s)	
Type of configuration	Software	
	Teach-in	
Operational controls	Membrane keyboard	
Environmental data		
Ambient temperature, operation	-30 60 °C	
Ambient temperature, operation Ambient temperature, storage	-30 60 °C -40 70 °C	
Ambient temperature, storage		
Ambient temperature, storage		
Ambient temperature, storage Certifications	-40 70 °C	
Ambient temperature, storage Certifications Degree of protection	-40 70 °C IP 65	_
Ambient temperature, storage Certifications Degree of protection Protection class	-40 70 °C IP 65 III	

Customs tariff number	90314990
ECLASS 5.1.4	27270910
ECLASS 8.0	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ECLASS 13.0	27270910
ECLASS 14.0	27270910
ECLASS 15.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549

Dimensioned drawings

All dimensions in millimeters



- Measurement field length 1760 mm
- F M6 thread
- G Fastening groove
- Transmitter
- R Receiver
- 5 mm Υ

Leuze

С

Dimensioned drawings

В

Electrical connection

R

A

Connection 1

Type of connection

Thread size

No. of pins

Encoding

Туре Material

Pin

1 2

3

4

Function

GND
IO-Link

V+

I/O 1


Pin assignment

- 5 I/O 2 6 RS 485 Tx+ 7 RS 485 Tx+
- 8 FE/SHIELD

Connection 2	X2A
Function	BUS IN
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded

Pin Pin assignment

1	TD0+		
2	RD0+		
3	TD0-		
4	RD0-		



PWR / SW IN / OUT А

Configuration interface Connection to transmitter

X1

Signal IN Signal OUT Voltage supply

Connector


M12 Male


Metal

8 -pin

A-coded








Electrical connection

X2B

Connection 3

Function	BUS OUT
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded

Pin	Pin assignment
1	TD0+
2	RD0+
3	TD0-
4	RD0-



Operation and display

LED	Display	Meaning
1	Green, continuous light	Operational readiness
	Green, flashing	Teach / error
2	Yellow, continuous light	Light path free, with function reserve
	Yellow, flashing	No function reserve
	Off	Object detected
3	Green, continuous light (at the X2A / X2B connector)	Link
4	Yellow, continuous light (at the X2A / X2B connector)	Activity


Suitable transmitters

 Part no.	Designation	Article	Description
50118959	CML730i-T10- 1760.R-M12	Light curtain transmitter	Operating range: 0.3 9.5 m Connection: Connector, M12, Rear side, 5 -pin

Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle Measuring light curtain
7XXi	Series 720i: 720i series 730i: 730i series
Y	Device type T: transmitter R: receiver
22	Beam spacing 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm
AAAA	Measurement field length [mm], dependent on beam spacing
В	Equipment A: Axial connector outlet R: Rear connector outlet





Part number code



CCC	Interface L: IO-Link //N: CANopen /PB: PROFIBUS /PN: PROFINET //CV: Analog current and voltage output
	/D3: RS 485 Modbus
DDD	Special equipment -PS: Power Setting
EEE	Electrical connection M12: M12 connector
FFF	-EX: Explosion protection
	Note
1	A list with all available device types can be found on the Leuze website at www.leuze.com.

Notes

Observe intended use!
 This product is not a safety sensor and is not intended as personnel protection. The product may only be put into operation by competent persons. Only use the product in accordance with its intended use.

For UL applications:

🗞 For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).

These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

Accessories

Connection technology - Connection cables

 Part no.	Designation	Article	Description
50132079	KD U-M12-5A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC
50135074	KS ET-M12-4A-P7- 050	Connection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connector, LED: No Connection 2: Open end Shielded: Yes Cable length: 5.000 mm Sheathing material: PUR

Accessories

Leuze

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50135081	KSS ET-M12-4A- RJ45-A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: RJ45 Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Connection technology - Y distribution cables

	Part no.	Designation	Article	Description
	50118183	K-Y1 M12A-5m- M12A-S-PUR	Interconnection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin Connection 3: Connector, M12, Axial, Female, A-coded, 8 -pin Shielded: Yes Cable length fork 1: 5,000 mm Cable length fork 2: 150 mm Sheathing material: PUR

Mounting technology - Mounting brackets

 Part no.	Designation	Article	Description
 50142900	BT 700M.5-2SET	Mounting device set	Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel

Mounting technology - Swivel mounts

	Part no.	Designation	Article	Description
RR.	429029	BT-2RG	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

Configuration devices

 Part no.	Designation	Article	Description
50121098	SET MD12-US2-IL1.1 + Zub.	Diagnostics set	Interface: USB Connections: 2 Piece(s) Degree of protection: IP 20

Accessories

Leuze

Services

 Part no.	Designation	Article	Description
S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

	Note
6	♣ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.