

## Technical data sheet

### Mounting device

Part no.: 50060503

BT 20-D12

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

# Technical data

## Basic data

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Contains</b>                   | 2x M3 mounting nut             |
|                                   | 2x M3 x 16 screw               |
|                                   | 2x M3 x 6 screw                |
|                                   | 2x position washers            |
| <b>Suitable for product group</b> | Stationary bar code readers    |
| <b>Suitable for</b>               | 25 series sensors              |
|                                   | BCL 2x series bar code readers |

## Mechanical data

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Design of mounting device</b>    | Mounting system      |
| <b>Type of fastening, at system</b> | For 12 mm rod        |
|                                     | Sheet-metal mounting |
| <b>Type of fastening, at device</b> | Screw type           |
| <b>Mounting device material</b>     | Metal                |

## Classification

|                              |          |
|------------------------------|----------|
| <b>Customs tariff number</b> | 83024900 |
| <b>ECLASS 5.1.4</b>          | 27279202 |
| <b>ECLASS 8.0</b>            | 27279202 |
| <b>ECLASS 9.0</b>            | 27273701 |
| <b>ECLASS 10.0</b>           | 27273701 |
| <b>ECLASS 11.0</b>           | 27273701 |
| <b>ECLASS 12.0</b>           | 27273701 |
| <b>ECLASS 13.0</b>           | 27273701 |
| <b>ECLASS 14.0</b>           | 27273701 |
| <b>ETIM 5.0</b>              | EC002498 |
| <b>ETIM 6.0</b>              | EC003015 |
| <b>ETIM 7.0</b>              | EC003015 |
| <b>ETIM 8.0</b>              | EC003015 |
| <b>ETIM 9.0</b>              | EC003015 |

# Dimensioned drawings

All dimensions in millimeters

