


## Technical data sheet Interconnection cable

Part no.: 50137080

KSS ET-M12-4A-M12-4A-P7-150

### Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



## Technical data

### Basic data

Application	Oil and lubricant resistant
Suitable for interface	Ethernet

### Electrical data

#### Performance data

Operating voltage	60 V DC
-------------------	---------

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Version	Axial
Connector, LED	No

#### Connection 2

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Version	Axial

#### Cable properties

Number of conductors	4 Piece(s)
Wire cross section	0.34 mm <sup>2</sup>
AWG	22
Sheathing color	Green
Shielded	Yes
Silicone-free	Yes
Cable design	Interconnection cable
Cable diameter (external)	6.7 mm
Cable length	15,000 mm
Sheathing material	PUR
Wire insulation	PP
Suitability for drag chains	Yes
Traverse rate	Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 2m/s <sup>2</sup>

Properties of the outer sheathing	Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable
-----------------------------------	--

Resistance of the outer sheathing	Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2
-----------------------------------	---

### Mechanical data

Width across flats	13 mm
Bending cycles	2,000,000 Piece(s)
Bending radius, flexible laying, min.	One-time min. 5 x cable diameter
Bending radius, stationary laying, min.	One-time min. 5 x cable diameter

### Operation and display

#### Environmental data

Ambient temperature, operation, flexible use	-20 ... 60 °C
Ambient temperature, operation, stationary use	-20 ... 60 °C

#### Certifications

Degree of protection	IP 67
----------------------	-------

#### Classification

Customs tariff number	85444290
ECLASS 5.1.4	27279201
ECLASS 8.0	27279218
ECLASS 9.0	27060311
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855

# Electrical connection

## Connection 1


Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Version	Axial
Connector, LED	No

## Connection 2

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	4 -pin
Encoding	D-coded
Version	Axial

# Circuit diagrams

## Wiring schematic



- a TD+
- b RD+
- c TD-
- d RD-
- e Shield