

Technical data sheet


Connection cable

Part no.: 50137381

KS GB-M12-8A-P7-300

Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



Technical data

Basic data

| | |
|------------------------|----------|
| Suitable for interface | Ethernet |
|------------------------|----------|

Electrical data

Performance data

| | |
|-------------------|------------------|
| Operating voltage | Max. 125 V AC/DC |
|-------------------|------------------|

Connection

Connection 1

| | |
|----------------------|--|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| Handle body material | PUR |
| No. of pins | 8 -pin |
| Encoding | X-coded |
| Version | Axial |
| Connector, LED | No |
| Lock | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

Connection 2

| | |
|--------------------|----------|
| Type of connection | Open end |
|--------------------|----------|

Cable properties

| | |
|-----------------------------------|--|
| Number of conductors | 8 Piece(s) |
| Wire cross section | 0.14 mm ² |
| AWG | 26 |
| Sheathing color | Green |
| Shielded | Yes |
| Silicone-free | Yes |
| Cable design | Connection cable (open on one end) |
| Cable diameter (external) | 6.4 mm |
| Cable length | 30,000 mm |
| Sheathing material | PUR |
| Wire insulation | PE |
| Suitability for drag chains | No |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone and lead, easily machine-processable |
| Resistance of the outer sheathing | Good oil, gasoline and chemical resistance in accordance with VDE 072, flame retardant in accordance with IEC 60332 / VDE 0472 |

Mechanical data

| | |
|---|--------------------------|
| Width across flats | 13 mm |
| Bending radius, flexible laying, min. | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 5 x cable diameter |

Operation and display

Environmental data

| | |
|--|---------------|
| Ambient temperature, operation, flexible use | -5 ... 70 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

Certifications

| | |
|----------------------|-------|
| Degree of protection | IP 65 |
| | IP 67 |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4 | 27279201 |
| ECLASS 8.0 | 27279218 |
| ECLASS 9.0 | 27060311 |
| ECLASS 10.0 | 27060311 |
| ECLASS 11.0 | 27060311 |
| ECLASS 12.0 | 27060311 |
| ECLASS 13.0 | 27060311 |
| ECLASS 14.0 | 27060311 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |
| ETIM 8.0 | EC001855 |
| ETIM 9.0 | EC001855 |

Electrical connection

Connection 1

| | |
|----------------------|--|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| Handle body material | PUR |
| No. of pins | 8 -pin |
| Encoding | X-coded |
| Version | Axial |
| Connector, LED | No |
| Lock | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

Electrical connection

Connection 2

Type of connection

Open end

Circuit diagrams

Wiring schematic

