

## Technical data sheet

### Base station

Part no.: 50144935

Base IT 1991i

#### Contents

- Technical data
- Electrical connection
- Operation and display
- Notes
- Accessories



For illustration purposes only



## Technical data

### Basic data

Type	Base station
Suitable for	IT 1991i series mobile 2D-code readers

### Electrical data

#### Performance data

Supply voltage $U_B$	4.5 ... 5.5 V, DC
----------------------	-------------------

### Interface

Type	PS/2
	RS 232
	USB

### Connection

Number of connections	3 Piece(s)
Bluetooth range	Class 1
Bluetooth version	4.2

#### Connection 1

Function	Configuration interface
	Data interface
	Voltage supply

Type of connection	RJ41
--------------------	------

#### Connection 2

Function	Voltage supply
Type of connection	Jack socket

#### Connection 3

Type of connection	Bluetooth
--------------------	-----------

### Mechanical data

Dimension (W x H x L)	102 mm x 60 mm x 245 mm
Plastic housing	UL 94-V0
Net weight	290 g

### Environmental data

Ambient temperature, operation	-20 ... 50 °C
Ambient temperature, storage	-40 ... 60 °C
Drop height	1.2 m
Measurements relative to	Concrete floor

### Certifications

Degree of protection	IP 51
----------------------	-------

### Classification

Customs tariff number	84719000
ECLASS 5.1.4	27289200
ECLASS 8.0	27289290
ECLASS 9.0	27289290
ECLASS 10.0	27280192
ECLASS 11.0	27280192
ECLASS 12.0	27280192
ECLASS 13.0	27280192
ECLASS 14.0	27280192
ETIM 5.0	EC002498
ETIM 6.0	EC002997
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015


## Electrical connection

### Connection 1

Function	Configuration interface
	Data interface
	Voltage supply
Type of connection	RJ41

### Pin Pin assignment

1	Shield
2	Cable ID
3	GND
4	TxD RS 232 / n.c. USB
5	RxD RS 232 / n.c. USB
6	CTS RS 232 / n.c. USB
7	+5 V DC
8	RTS RS 232 / n.c. USB
9	n.c. RS 232 / Data + USB
10	n.c. RS 232 / Data - USB



## Electrical connection

### Connection 2

Function	Voltage supply
Type of connection	Jack socket
Diameter	5.4
No. of pins	2 -pin


### Connection 3

Function	Configuration interface Data interface
Type of connection	Bluetooth

## Operation and display


LED	Display	Meaning
1	Red, 1x flashing Red, continuous light	Data transmission active Operational readiness
2	Green, flashing Green, continuous light	Charging active Battery charged

## Notes


⚠ Observe intended use!	
	<ul style="list-style-type: none"> <li>⌘ This product is not a safety sensor and is not intended as personnel protection.</li> <li>⌘ The product may only be put into operation by competent persons.</li> <li>⌘ Only use the product in accordance with its intended use.</li> </ul>

## Accessories

### Connection technology - Connection unit


	Part no.	Designation	Article	Description
	50112891	MA 248i Profinet Gateway	Modular connection unit	Supply voltage: 18 ... 30 V Current consumption, max.: 300 mA Interface: PROFINET, RS 232 Connections: 6 Piece(s) Degree of protection: IP 65

### Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50113397	KB JST-HS-300	Interconnection cable	Suitable for interface: RS 232 Connection 1: JST ZHR Connection 2: Sub-D, Axial, Male, 9 -pin Shielded: Yes Cable length: 300 mm Sheathing material: PUR

## Accessories

### Power supply units

	Part no.	Designation	Article	Description
	50123862	NT Base IT1911-EU	Power supply unit	Type of power supply unit: Plug-in power supply unit Output: 5 V DC, 1 A Input: 110 ... 240 V AC, 50 ... 60 Hz

#### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.