


Technical data sheet Interconnection cable

Part no.: 50144648

KSS ET-RJ45-A-RJ45-A-P7-005-R

Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



Technical data

Basic data

Application	Oil and lubricant resistant
Suitable for interface	Ethernet

Electrical data

Performance data	
Operating voltage	60 V DC

Connection

Connection 1	
Type of connection	Connector
Connector, LED	No
Version	Axial
No. of pins	4 -pin
Type	Male
Connection 2	
Type of connection	RJ45
Type	Male
No. of pins	4 -pin
Version	Axial
Cable properties	
Number of conductors	4 Piece(s)
Wire cross section	0.34 mm ²
AWG	22
Sheathing color	Green
Shielded	Yes
Silicone-free	Yes
Cable design	Interconnection cable
Cable diameter (external)	6.7 mm
Cable length	500 mm
Sheathing material	PUR
Wire insulation	PP
Traverse rate	Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 2m/s ²
Suitability for drag chains	Yes
Properties of the outer sheathing	Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable
Resistance of the outer sheathing	Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2
Torsion suitability	±180° / m (max. 1 mio. cycles with 20 cycles / min)

Mechanical data

Width across flats	13 mm
Bending radius, flexible laying, min.	One-time min. 12 x cable diameter
Bending radius, stationary laying, min.	One-time min. 8 x cable diameter

Operation and display

Environmental data

Ambient temperature, operation, flexible use	-10 ... 50 °C
Ambient temperature, operation, stationary use	-40 ... 80 °C

Certifications

Degree of protection	IP 20 (RJ 45)
	IP 65
	IP 67

Classification

Customs tariff number	85444290
ECLASS 5.1.4	27279201
ECLASS 8.0	27279218
ECLASS 9.0	27060311
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ECLASS 15.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855
ETIM 10.0	EC001855

Electrical connection

Connection 1

Type of connection	Connector
Connector, LED	No
Version	Axial
No. of pins	4 -pin
Type	Male

Electrical connection

Connection 2

Type of connection	RJ45
--------------------	------

Circuit diagrams

Wiring schematic

