

Technical data sheet

Glass fiber optics type diffuse reflective

Part no.: 50153815

GF-ETB-SS-630-SM

Contents

- Technical data
- Dimensioned drawings
- Notes
- Further information



For illustration purposes only

Technical data

Basic data

Series	GF
Operating principle	Diffuse reflection principle
Area of application	General applications

Special version

Special version	Heat resistant
-----------------	----------------

Optical data

Opening angle	60 °
Light beam exit	Front
Fiber core	Mixed fiber configuration Multiple fiber core
Fiber core material	Glass
Active fiber diameter	1 mm
Operating range with LV461	2 ... 60 mm
Operating range with LV462	2 ... 100 mm
Operating range with LV463	2 ... 180 mm
Operating range with LV463.XV	3 ... 305 mm
Operating range with LV463.XR	5 ... 450 mm

Connection

Connection, amplifier side	Ø 2.2 mm
----------------------------	----------

Mechanical data

Design	Cylindrical
Outer diameter	2.9 mm
Head material	Stainless steel (SUS303)
Type	Glass fiber optics (GF)
Fiber length	3,000 mm
Fiber sheathing material	Stainless steel (SUS303)
Fastening of the probe	M6
Smallest bending radius (static)	R23
Smallest bending radius (moving)	R23
Sleeve length at optical outlet	33 mm
Metric thread on fiber optic sleeve	Yes
Laying	standard


Environmental data

Ambient temperature, operation	-40 ... 250 °C
--------------------------------	----------------

Classification

Customs tariff number	90011090
ECLASS 5.1.4	27270905
ECLASS 8.0	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905
ECLASS 11.0	27273606
ECLASS 12.0	27273606
ECLASS 13.0	27273606
ECLASS 14.0	27273606
ECLASS 15.0	27273606
ECLASS 16.0	27273606
ETIM 5.0	EC002651
ETIM 6.0	EC002651
ETIM 7.0	EC002651
ETIM 8.0	EC002651
ETIM 9.0	EC002651
ETIM 10.0	EC002651

All dimensions in millimeters



Observe intended use!



- ⚠ This product is not a safety sensor and is not intended as personnel protection.
- ⚠ The product may only be put into operation by competent persons.
- ⚠ Only use the product in accordance with its intended use.

- Suitable products for operating these fiber optics are the fiber optic amplifiers LV461, LV462B as well as LV463, LV463.XV and LV463.XR.
- Operating range measured on a white object (90% diffuse reflection) with the following settings on the fiber optic amplifier:
 - max. response time
 - max. amplification
 - min. switching threshold